



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BKFD125 PRL1A/2A Universal Main BKR Kit 480V 1 or 3PH Fram

Eaton Corp

Catalog Number	BKFD125
Manufacturer	Eaton Corp
Description	Eaton Pow-R-Stock Series Main Circuit Breaker Kit, FD Circuit BKR Type, Top and Bottom Mounting, Top and Bottom, Single- or Three-Phase, 125a
Weight per unit	12.0 (lbs/each)
Product Category	Main Circuit Breaker Modules

Features

dimensions	3.9000 IN X 4.1300 IN X 6.0000 IN
media	Yes
Phase	Single-phase, three-phase

Descriptions

Description	PRL1A/2A UNIVERSAL MAIN BKR KIT 480V 1 OR 3PH FRAM
extra long description	ETN BKFD125 PRL1A/2A Main BKR KIT 4
Features	Panelboards Pow-R-Stock Plus Program provide interiors; type 1 and 3R boxes; surface and flush trims; factory-assembled panelboards; main breaker kits; branch breakers; lug kits; service entrance kits; ground kits; and 200% neutral kits. In addition, the distributor stocking program can be used with various Eaton commercial distribution products and is designed to meet UL67 standards for use in data center, industrial, commercial and healthcare facilities.
Long Description	Eaton Pow-R-stock series Main circuit breaker kit, FD circuit bkr type, Top and Bottom Mounting, Top and Bottom, Single- or three-phase, 125A
Product Type	PRL1A/2A Main BKR Kit 480V 1_3PH FD3125

Manufacturer Information

Brand	Eaton
GTIN	00786689030889
Manufacturers Part Number	BKFD125
UPC	786689030889

Taxonomies, Classifications, and Categories

Category Description	Breaker Connector and Mounting Kits & Other Accessories
Type	Accessory

Packaging

Carton	1
Weight Per each	12



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting	Top, bottom
standard	UL Listed