



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BGA0501420 1/2" Alu GRND Bushing

Abb Installation Products, Inc

| | |
|------------------|--|
| Catalog Number | BGA0501420 |
| Manufacturer | Abb Installation Products, Inc |
| Description | 1/2 Inch Blackjack Grounding Bushing, Aluminum, Galvanized, Wire Range 14 to 2/0 For Use With Threaded or Threadless Rigid/Imc Conduit |
| Weight per unit | 0.0600 (lbs/each) |
| Product Category | Aluminum |

Features

| | |
|----------|----------|
| Material | Aluminum |
|----------|----------|

Material, Color, and Finish

| | |
|--------|------------|
| Finish | Galvanized |
|--------|------------|

Dimensions and Weight

| | |
|------|----------|
| Size | 1/2 INCH |
|------|----------|

Descriptions

| | |
|------------------------|--|
| Description | 1/2" ALU GRND BUSHING |
| extra long description | ABB BGA050-14-20 1/2 INCH GROUND BU |
| Long Description | 1/2 Inch Blackjack Grounding Bushing, Aluminum, Galvanized, Wire Range 14 to 2/0 for Use with Threaded or Threadless Rigid/IMC Conduit |
| Product Type | 1/2 Inch Ground Bushing Aluminum |
| Special Features | Grounding Bushings & Accessories |

Manufacturer Information

| | |
|---------------------------|-----------------|
| Brand | T&B Ind Fitting |
| GTIN | 00786210162904 |
| Manufacturers Part Number | BGA050-14-20 |
| UPC | 786210162904 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | COUPLINGS, ADAPTERS, REDUCERS, BUSHINGS, & CAPS |
| Type | Grounding Bushings & Accessories |

Packaging

| | |
|-----------------|------|
| Carton | 50 |
| Package | 100 |
| Weight Per each | 0.06 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|--------------------------------|
| Application | For use with rigid/IMC conduit |
| standard | UL E3060, CSA |