



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BQ240250 BQ Quad BRKR 1-40A/2P 1-50A/2P Indep. Trip 120/240

Eaton Corp

Catalog Number	BQ240250
Manufacturer	Eaton Corp
Description	Eaton BR Thermal Magnetic Circuit Breaker, Type BQ 1-Inch CTL Plug-On Circuit Breaker, Includes Rejection Tab Feature, (1) Two-Pole 40 A, (1) Two-Pole 50 A, 10 Kaic, Four-Pole, 120/240V, BQ, Independent, #14-4 Awg Cu/Al, Q28, BQ, Type BR Loadcenters
Weight per unit	0.8000 (lbs/each)
Product Category	Quadplex Standard Trip Plug-In

Features

dimensions	1.4000 IN X 3.2000 IN X 3.1000 IN
interrupt rating	10 kAIC
Poles	Four-pole
Trip Type	Independent
Voltage Rating	120/240 V

Descriptions

Description	BQ QUAD BRKR 1-40A/2P 1-50A/2P INDEP. TRIP 120/240
extra long description	ETN BQ240250 BQ Quad 1-40A/2P 1-50A
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR thermal magnetic circuit breaker, Type BQ 1-Inch CTL plug-on circuit breaker, Includes rejection tab feature, (1) Two-Pole 40 A, (1) Two-Pole 50 A, 10 kAIC, Four-pole, 120/240V, BQ, Independent, #14-4 AWG Cu/Al, Q28, BQ, Type BR Loadcenters
Product Type	BQ Quad 1-40A/2P 1-50A/2P 120/240V 10K
Special Features	Includes Rejection Tab feature

Manufacturer Information

Brand	Eaton
GTIN	00786676371209
Manufacturers Part Number	BQ240250
UPC	786676371209



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Specialty Breakers (Quad, Dupl, Shunt Trip)
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Weight Per each	0.8

Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative Energy Generation - Conventional Energy - Conventional Energy Other Datacenters - IT Space: CI and Hyper Converged Marine Vessels and Equipment - Marine Vessels and Equipment - Other
standard	UL 489, Federal Specifications Classification W-C375