



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR160 Type BR BRKR 60A/1 Pole 120/240V 10K

Eaton Corp

Catalog Number	BR160
Manufacturer	Eaton Corp
Description	Eaton BR Thermal Magnetic Circuit Breaker, Type BR 1-Inch Plug-On Circuit Breaker, 60 A, 10 Kaic, Single-Pole, 120/240V, BR, #4-1/0 Awg Cu/Al, BR, Type BR Loadcenters
Weight per unit	0.3000 (lbs/each)
Product Category	1 Pole Standard Trip Plug-In

Features

dimensions	3.0000 IN X 1.0000 IN X 3.0000 IN
interrupt rating	10 kAIC
Poles	1
Voltage Rating	120/240 V

Descriptions

Description	TYPE BR BRKR 60A/1 POLE 120/240V 10K
extra long description	ETN BR160 Type BR Breaker 60A/1 Pol
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 60 A, 10 kAIC, Single-pole, 120/240V, BR, #4-1/0 AWG Cu/Al, BR, Type BR Loadcenters
Product Type	Type BR Breaker 60A/1 Pole 120/240V 10K

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786676362351
Manufacturers Part Number	BR160
UPC	786676362351

Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Weight Per each	0.3



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Generation - Renewable Energy - Alternative Energy
Marine Vessels and Equipment - Marine Vessels and Equipment -
Other
Other Generation - Conventional Energy - Conventional
Energy
Datacenters - IT Space: CI and Hyper Converged

standard

UL 489, Federal Specifications Classification W-C375