



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BR4040B200V2 1PH 200A 40/40 MB Loadcenter

Eaton Corp

Catalog Number	BR4040B200V2
Manufacturer	Eaton Corp
Description	BR Style Load Center, 40 Spaces, 40 Circuits, 200 A, 120/240 V Ac, 2/0 Awg to 300 Kcmil Wire Size, Metallic Material, Copper Bus Material
Weight per unit	42.4 (lbs/each)
Product Category	Single Phase Main Breaker Load

Features

amperage rating	59120
Box Size	D1r
cover	Cover included
Cover Type	Cover included
dimensions	5.1900 IN X 14.3100 IN X 29.1300 IN
main circuit breaker	BWH
Number of Wires	Three-wire
Phase	1 PH
used with	Type BR 1-inch breakers

Material, Color, and Finish

Enclosure Material	Metallic
--------------------	----------

Dimensions and Weight

Size	D1r
------	-----

Descriptions

Description	1PH 200A 40/40 MB LOADCENTER
extra long description	ETN BR4040B200V2 BR style 1-inch lo

Manufacturer Information

GTIN	00782114894484
UPC	782114894484

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
igcc	PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMESELECT[T] BRAND
Type	Main circuit breaker
unspsc code	MODULAR LINE CORD, TELEPHONE LINE EXTENSION CORD TYPE; 15 FT LENGTH IN FT; METALLIC COLOR FAMILY; SILVER MANUFACTURERS COLOR NAME; GC[T] BRAND; CONNECTOR TYPE MODULAR PLUG; CORD SIZE (6) 26 AWG



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	42.36

Uses, Certifications, and Standards

Application	Power Distribution
Enclosure standard	NEMA 1 UL 67; UL 50