

# Specifications



Photo is representative



## Eaton BRCAF120

Eaton BR AFCI circuit breaker, Arc fault, 20A, 10 kAIC, Single-pole, 120V, BR, #14-4 AWG Cu/Al, Type BR Loadcenters

### General specifications

<b>PRODUCT NAME</b>	Eaton BR AFCI circuit breaker
<b>CATALOG NUMBER</b>	BRCAF120
<b>UPC</b>	786685514338
<b>PRODUCT LENGTH/DEPTH</b>	6 in
<b>PRODUCT HEIGHT</b>	1.25 in
<b>PRODUCT WIDTH</b>	3.5 in
<b>PRODUCT WEIGHT</b>	0.45 lb
<b>WARRANTY</b>	Limited lifetime residential, 1 year commercial
<b>COMPLIANCES</b>	Federal Specifications Classification W-C375
<b>CERTIFICATIONS</b>	UL 1699

## Product specifications

USED WITH	Type BR Loadcenters
AMPERAGE RATING	20 A
VOLTAGE RATING	120 V
INTERRUPT RATING	10 kAIC
MAIN CIRCUIT BREAKER	BR
WIRE SIZE	#14-4 AWG Cu/Al
NUMBER OF POLES	Single-pole
SPECIAL FEATURES	Arc fault

## Resources

CATALOGS	<a href="#">Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - BRCAF120</a>
WARRANTY GUIDES	<a href="#">Eaton type BR circuit breaker limited warranty June 2024</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications



Photo is representative



## Eaton BRCAF120

Eaton BR AFCI circuit breaker, Arc fault, 20A, 10 kAIC, Single-pole, 120V, BR, #14-4 AWG Cu/Al, Type BR Loadcenters

### General specifications

<b>PRODUCT NAME</b>	Eaton BR AFCI circuit breaker
<b>CATALOG NUMBER</b>	BRCAF120
<b>UPC</b>	786685514338
<b>PRODUCT LENGTH/DEPTH</b>	6 in
<b>PRODUCT HEIGHT</b>	1.25 in
<b>PRODUCT WIDTH</b>	3.5 in
<b>PRODUCT WEIGHT</b>	0.45 lb
<b>WARRANTY</b>	Limited lifetime residential, 1 year commercial
<b>COMPLIANCES</b>	Federal Specifications Classification W-C375
<b>CERTIFICATIONS</b>	UL 1699

## Product specifications

USED WITH	Type BR Loadcenters
AMPERAGE RATING	20 A
VOLTAGE RATING	120 V
INTERRUPT RATING	10 kAIC
MAIN CIRCUIT BREAKER	BR
WIRE SIZE	#14-4 AWG Cu/Al
NUMBER OF POLES	Single-pole
SPECIAL FEATURES	Arc fault

## Resources

CATALOGS	<a href="#">Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - BRCAF120</a>
WARRANTY GUIDES	<a href="#">Eaton type BR circuit breaker limited warranty June 2024</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

