



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BR1632B200 16/32C 200A 1PH MB Loadcenter

*Eaton Corp*

|                  |                                                                                                                                                                                                              |
|------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | BR1632B200                                                                                                                                                                                                   |
| Manufacturer     | Eaton Corp                                                                                                                                                                                                   |
| Description      | BR Style 1-Inch Loadcenter, Main Circuit Breaker, No Feed-Thru Lugs, 200A, Single-Phase, 32-Pole, 32 Circuits, 16 Spaces, 120/240V, #2/0-300 Kcmil Cu/Al At 60°C or 75°C Wire, Nema 1 Enclosure, C4 Box Size |
| Weight per unit  | 27.4 (lbs/each)                                                                                                                                                                                              |
| Product Category | Single Phase Main Breaker Load                                                                                                                                                                               |

### Features

|                      |                                      |
|----------------------|--------------------------------------|
| amperage rating      | 59120                                |
| Box Size             | HID Floodlight                       |
| cover                | Cover included                       |
| Cover Type           | Cover included                       |
| dimensions           | 5.0000 IN X 13.0000 IN X 15.0000 IN  |
| interrupt rating     | 25 kAIC                              |
| main circuit breaker | BWH                                  |
| Number of Circuits   | 32 W                                 |
| number of spaces     | 16 OZ                                |
| Number of Wires      | Three-wire                           |
| Phase                | 1 PH                                 |
| used with            | Type BR 1-inch breakers              |
| Voltage Rating       | 120/240 VAC                          |
| Wire Size            | #2/0-300 kcmil Cu/Al at 60°C or 75°C |

### Material, Color, and Finish

|                    |          |
|--------------------|----------|
| Bus Material       | Aluminum |
| Enclosure Material | Metallic |

### Dimensions and Weight

|      |    |
|------|----|
| Size | C4 |
|------|----|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |                                                                                                                                                                                                              |
|------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description            | 16/32C 200A 1PH MB LOADCENTER                                                                                                                                                                                |
| extra long description | ETN BR1632B200 BR style 1-inch load                                                                                                                                                                          |
| Long Description       | BR style 1-inch loadcenter, main circuit breaker, no feed-thru lugs, 200A, single-phase, 32-pole, 32 circuits, 16 spaces, 120/240V, #2/0-300 kcmil Cu/Al at 60°C or 75°C wire, NEMA 1 enclosure, c4 box size |
| Product Type           | BR Style 1-Inch Loadcenter                                                                                                                                                                                   |
| Special Features       | No feed-thru lugs                                                                                                                                                                                            |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00786676445351 |
| Manufacturers Part Number | BR1632B200     |
| UPC                       | 786676445351   |

## Taxonomies, Classifications, and Categories

|                      |                                                                                                                                                                                                                        |
|----------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Category Description | LOADCENTERS & COVERS                                                                                                                                                                                                   |
| igcc                 | PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMeselect[T] BRAND |
| Type                 | Main circuit breaker                                                                                                                                                                                                   |
| unspsc code          | 39121101                                                                                                                                                                                                               |

## Availability

|        |          |
|--------|----------|
| Status | Inactive |
|--------|----------|

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight Per each | 27.4 |

## Uses, Certifications, and Standards

|                   |                             |
|-------------------|-----------------------------|
| Application       | Power Distribution          |
| Enclosure         | NEMA 1                      |
| Mounting standard | Combination<br>UL 67; UL 50 |