



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BR2040B200 20/40C 200A 1PH MB Loadcenter

Eaton Corp

|                  |  |
|------------------|--|
| Catalog Number   | BR2040B200   |
| Manufacturer     | Eaton Corp   |
| Description      | BR Style Load Center, 20 Spaces, 40 Circuits, 200 A, 120/240 V Ac, 2/0 Awg to 300 Kcmil Wire Size, Metallic Material, Aluminum Bus Material, 14.31 In Overall Length, 3.88 In Overall Width, 29.13 In Overall Height |
| Weight per unit  | 30.6 (lbs/each)  |
| Product Category | Single Phase Main Breaker Load   |

### Features

|                      |   |
|----------------------|---|
| amperage rating      | 59120   |
| Box Size             | LIGHTING TRACK, MINIATURE TYPE; EXTRUDED ALUMINUM MATERIAL; SATIN WHITE FINISH; 90-5/8 INCH; 1-3/8 INCH; 11/16 INCH; 8 FT NOMINAL LENGTH; UL, CSA APPROVAL; 20 AMPERE CURRENT RATING; 2 CIRCUIT(S); HALO[R], POWER-TRAC BRAND; WALL THICKNESS 0.06 INCH |
| cover                | Cover included  |
| Cover Type           | Cover included  |
| dimensions           | 98.5520millimetreX36.3474centimetreX47.6250centimetre   |
| main circuit breaker | BWH   |
| Number of Wires      | Three-wire  |
| Phase                | 1 PH  |
| used with            | Type BR 1-inch breakers   |

### Material, Color, and Finish

|                    |          |
|--------------------|----------|
| Enclosure Material | Metallic |
|--------------------|----------|

### Dimensions and Weight

|      |               |
|------|---------------|
| Size | F3003/4 YL105 |
|------|---------------|

### Descriptions

|                        |                                     |
|------------------------|-------------------------------------|
| Description            | 20/40C 200A 1PH MB LOADCENTER       |
| extra long description | ETN BR2040B200 BR style 1-inch load |

### Manufacturer Information

|      |                |
|------|----------------|
| GTIN | 00786676445559 |
| UPC  | 786676445559   |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | LOADCENTERS & COVERS  |
| igcc                 | PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL;<br>WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL;<br>125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT<br>RESISTANT; (2) 18 AWG CORD SIZE; HOMeselect[T] BRAND |
| Type                 | Main circuit breaker  |
| unspsc code          | 39121101  |

## Packaging

|                 |       |
|-----------------|-------|
| Carton          | 1     |
| Weight Per each | 30.58 |

## Uses, Certifications, and Standards

|           |             |
|-----------|-------------|
| Enclosure | NEMA 1      |
| Mounting  | Combination |
| standard  | UL 67;UL 50 |