



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BR4242L225G 42/42C 225A Mlo Loadcenter W/Ground

*Eaton Corp*

Catalog Number	BR4242L225G
Manufacturer	Eaton Corp
Description	Main Lug Load Center, 42 Spaces, 42 Circuits, 225 A, 120/240 V Ac, #1 Awg to 300 Kcmil Wire Size, Metallic Material, Aluminum Bus Material
Weight per unit	37.0 (lbs/each)
Product Category	Single Phase Main Lug Load Cen

### Features

amperage rating	225 Im
Box Size	5 in
cover	Cover not included
Cover Type	Cover not included
dimensions	5.2000 IN X 14.3000 IN X 39.0000 IN
main circuit breaker	CEMAT RSRT9 V7.0 OS SOFTWARE
number of spaces	42 WTT
Number of Wires	Three-wire
Phase	1 PH
used with	Type BR 1-inch breakers

### Material, Color, and Finish

Enclosure Material	Metallic
--------------------	----------

### Dimensions and Weight

Size	5 kVA kVA
------	-----------

### Descriptions

Description	42/42C 225A MLO LOADCENTER W/GROUND
extra long description	ETN BR4242L225G Eaton BR style 1-in
Special Features	Current design

### Manufacturer Information

GTIN	00782116946396
UPC	782116946396



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
igcc	PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMESELECT[T] BRAND
Type	MAIN LUG
unspsc code	39121101

## Availability

Status	Inactive
--------	----------

## Packaging

Carton	1
Weight Per each	37

## Uses, Certifications, and Standards

Enclosure	NEMA 1
Mounting	Surface mounting
standard	UL 67; UL 50