



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BT1.5IC 6" NylIn CBL Tie SS Barb Int Cross Sec WHT *Panduit Corporation*

Catalog Number	BT1.5IC
Manufacturer	Panduit Corporation
Description	The BT1.5I-C Dome-Top® Barb Ty, Features A Unique Patented Design With Its Round Smooth Edges. Paired With The Stainless-Steel Locking Barb, These Cable Ties Provide Consistent Performance, Reliability and Infinite Adjustability Through The Entire Bundle Range. Intermediate Cross Section, 6.1" (155MM) Length. Appropriate For Indoor Use, Made Of Nylon 6.6, Are Natural In Color and Come In Packages Of 100.
Weight per unit	0.2000 (lbs/each)
Product Category	Cable Ties & Wraps

### Features

media	Yes
Tensile Strength	40

### Dimensions and Weight

Length	6.1
Thickness	0.04

### Descriptions

Description	6" NYLIn CBL TIE SS BARB INT CROSS SEC WHT
extra long description	PAN BT1.5I-C Dome-Top® BT1.5I-C Bar
Long Description	The BT1.5I-C Dome-Top® barb ty, features a unique patented design with its round smooth edges. Paired with the stainless-steel locking barb, these cable ties provide consistent performance, reliability and infinite adjustability through the entire bundle range. Intermediate cross section, 6.1" (155mm) length. Appropriate for Indoor use, made of Nylon 6.6, are natural in color and come in packages of 100.
Product Type	Dome-Top® BT1.5I-C Barb Tie, PA6.6, 6.1"L, 40LB, PK100
Special Features	Indoor

### Manufacturer Information

Brand	PANDUIT
GTIN	00074983413331
Manufacturers Part Number	BT1.5I-C
UPC	074983413331

### Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Cable Tie



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Availability

minimum qty ..... 100

## Packaging

Carton ..... 100

Package ..... 1000

Weight Per each ..... 0.2

## Uses, Certifications, and Standards

standard ..... UL 62275 (File E56854), CSA-C22.2 No. 62275, 11130200, NRC  
10CFR50, QPL-AS23190, CSA Certified, RoHS Compliant