



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BRH260 Type BR BRKR 60A/2 Pole Com. Trip 120/240V 22K

Eaton Corp

Catalog Number	BRH260
Manufacturer	Eaton Corp
Description	Eaton BR Thermal Magnetic Circuit Breaker, Type BR 1-Inch Plug-On Circuit Breaker, 60 A, 22 Kaic, Two-Pole, 120/240V, BRH, Common Breaker Trip, #4-1/0 Awg Cu/Al, Q28, BRH, Type BR Loadcenters
Weight per unit	0.6000 (lbs/each)
Product Category	2 Pole Standard Trip Plug-In

Features

dimensions	2.0000 IN X 2.9000 IN X 2.5000 IN
interrupt rating	22 kAIC
Poles	2
Trip Type	Common breaker trip
Voltage Rating	120/240 V

Descriptions

Description	TYPE BR BRKR 60A/2 POLE COM. TRIP 120/240V 22K
extra long description	ETN BRH260 BR 60A/2 Pole Com. Trip
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 60 A, 22 kAIC, Two-pole, 120/240V, BRH, Common breaker trip, #4-1/0 AWG Cu/Al, Q28, BRH, Type BR Loadcenters
Product Type	BR 60A/2 Pole Com. Trip 120/240V 22K

Manufacturer Information

Brand	Eaton
GTIN	00786676373753
Manufacturers Part Number	BRH260
UPC	786676373753

Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
Type	Thermal magnetic circuit breakers



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.6

Uses, Certifications, and Standards

Application	Generation - Conventional Energy - Conventional EnergyGeneration - Renewable Energy - Alternative EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - OtherOther
standard	UL 490,Federal Specifications Classification W-C376