



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BW2S SPRG CBL Clip *Cooper B-Line/Cable Tray*

Catalog Number	BW2S
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series All Threaded Rod and Drop Wire Supports, Conduit and Cable, Flange, 1" Height, 1" Length, 1" Width, 0.038LBS, Rod and Wire Fasteners, .13" Min Mount Size, .38" Max Mount Size
Weight per unit	0.0004 (lbs/each)
Product Category	Anchors & Fasteners

Features

dimensions	1.0000 IN X 1.0000 IN X 1.0000 IN
------------	-----------------------------------

Material, Color, and Finish

Color	ZINC PHOSPHATE
Finish	Zinc Phosphate

Descriptions

Description	SPRG CBL CLIP
extra long description	B-LINE BW2S ROD & WIRE FS,#12 WIRE
Features	Whether you are suspending from a ceiling, beam, lathers channel, strut or purlin, Eaton can meet your need with time-saving solutions.
Long Description	Eaton B-Line series all threaded rod and drop wire supports, Conduit and cable, Flange, 1" Height, 1" Length, 1" Width, 0.038lbs, Rod and wire fasteners, .13" Min mount size, .38" Max mount size
Product Type	Rod & Wire FS, #12 Wire Thru 1/4" PLN Rod, 1/4"-20 X 3/8" SCRW

Manufacturer Information

Brand	Eaton
GTIN	00782051401561
Manufacturers Part Number	BW2S
UPC	782051401561

Taxonomies, Classifications, and Categories

Category Description	FASTENERS
Type	Rod and wire fastener

Packaging

Carton	1
Package	100
Weight Per each	0.0004



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Lighting and
Lighting ControlsCommercial / Institutional Buildings / Structures
- Commercial / Institutional Buildings / Structures -
OtherCommercial / Institutional Buildings / Structures -
Commercial/Inst Bldg Strctures - Aftermarket

standard

UL Listed