



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BRP20N200RG BR Pon Loadcntr 200A Convertible 20 Space N3R Grou

*Eaton Corp*

|                  |  |
|------------------|--|
| Catalog Number   | BRP20N200RG  |
| Manufacturer     | Eaton Corp   |
| Description      | Eaton BR Convertible Loadcenter, Ground Bar, Converible, 200 A, X5, Aluminum, Cover Included, Nema 3R, Metallic, 10 Kaic, BR, Combination, 40 Circuits, Single-Pole, 20 Spaces, Three-Wire, Single-Phase, Type BR 1-Inch Breakers, 120/240 V |
| Weight per unit  | 21.0 (lbs/each)  |
| Product Category | Single Phase Convertible Load  |

### Features

|                  |                |
|------------------|----------------|
| amperage rating  | 200            |
| Cover Type       | Cover included |
| interrupt rating | 10             |
| number of spaces | 20             |
| Phase            | 1              |
| Voltage Rating   | 120/240 V      |
| Wattage          | Single-pole    |

### Dimensions and Weight

|        |       |
|--------|-------|
| Depth  | 3.88  |
| Height | 29.13 |
| Size   | X5    |
| Width  | 14.31 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | BR PON LOADCNTR 200A CONVERTIBLE 20 SPACE N3R GROU  |
| extra long description | ETN BRP20N200RG BR PON LC,200A,CONV   |
| Features               | Specially designed for easy installation, Eaton's BR 1-inch load centers house the branch circuit breakers and the wiring required to distribute power to individual circuits. They serve as main breaker for service entrances or as main lug when adding circuits to existing service. The main breaker protects the entire panel and can be used as a service disconnect. The branch breakers protect the wires leading to individual electrical loads such as fixtures and outlets. |
| Long Description       | Eaton BR convertible loadcenter,Ground bar,Converible,200 A,X5,Aluminum,Cover included,NEMA 3R,Metallic,10 kAIC,BR,Combination,40 Circuits,Single-pole,20 Spaces,Three-wire,Single-phase,Type BR 1-inch breakers,120/240 V  |
| Product Type           | BR Pon LC, 200A, Conv, 20 Space, N3R, Ground  |
| Special Features       | Ground bar  |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00786689059309 |
| Manufacturers Part Number | BRP20N200RG    |
| UPC                       | 786689059309   |

## Taxonomies, Classifications, and Categories

|                      |                        |
|----------------------|------------------------|
| Category Description | LOADCENTERS & COVERS   |
| Type                 | Convertible loadcenter |

## Packaging

|                 |    |
|-----------------|----|
| Carton          | 1  |
| Weight Per each | 21 |

## Uses, Certifications, and Standards

|                   |   |
|-------------------|---|
| Application       | Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other |
| Mounting standard | Combination Mount<br>UL 50,UL 67  |