



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **C25DND325A Pen N-R 3P 25A DP Cont SCR/PP W/QC Term 120VAC Coi** *Eaton Corp*

Catalog Number	C25DND325A
Manufacturer	Eaton Corp
Description	Eaton Definite Purpose Contactor, Quick, 25A, 110-120 Vac, 50/60 HZ, Open With Metal Mounting Plate, 15-50A, Two- and Three-Pole, 25A, Contactor, Three-Pole, 35A, Screw/Pressure Plate and Quick Connect Terminal (Side-By-Side), Non-Reversing
Weight per unit	1.2 (lbs/each)
Product Category	Definite Purpose Contactors

### **Features**

connection	Quick
dimensions	3.3500 IN X 2.4000 IN X 2.5000 IN
Enclosure Type	Open with metal mounting plate

### **Descriptions**

Description	PEN N-R 3P 25A DP CONT SCR/PP W/QC TERM 120VAC COI
extra long description	ETN C25DND325A PEN N-R 3P 25ADPCNT
Features	Definite purpose contactors and starters are electrically operated switching devices specifically designed for the heating, ventilation, air conditioning and refrigeration (HVAC) industry.
Long Description	Eaton definite purpose contactor, Quick, 25A, 110-120 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, 25A, Contactor, Three-pole, 35A, Screw/pressure plate and quick connect terminal (side-by-side), Non-reversing
Product Type	Pen N-R 3P 25ADPCNT SCR/PP W/Qc120ac

### **Manufacturer Information**

Brand	Eaton
GTIN	00782116300501
Manufacturers Part Number	C25DND325A
UPC	782116300501

### **Taxonomies, Classifications, and Categories**

Category Description	DP CONTACTORS
Type	Definite purpose contactor

### **Packaging**

Carton	1
Weight Per each	1.19



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels  
and OEMs

standard

CSA Certified,UL Recognized,RoHS Compliant