



## CAST WEATHERPROOF 2 GANG COVER, GRAY

CA2GS | [Pass & Seymour](#)

### FEATURES & BENEFITS

Cast Weatherproof Cover 2 Gang 2 Toggles with 15A 120VAC Single Pole Toggle Switches, 4 Screw Mounting, Gray



- Broad line of two gang covers for switches, receptacles, GFCIs, and power outlets.
- Baked-on electrostatic, polyester, powder paint for superior scratch and corrosion resistance.
- Heavy-duty die-cast zinc.
- Stainless steel springs.
- All covers have 2 self-closing lids.
- Covers comply with 2005 NEC Section 406.8(A) and 406.8(B)(2).

### SPECIFICATIONS

#### GENERAL INFO

Color: Gray

Type: Covers

Special Features: Weatherproof

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No

CUL Listing No: No

cULus: No

cURus: No

Federal Spec: No

UL Listing No: No

UN SPSC: 39121305

UR: No

## DIMENSIONS

Height (US): 4.52"

Width (US): 4.58"

## TECHNICAL INFORMATION

Material: Cast

Capacity: 2-gang

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: INDIA

Buy American Act Status: No



## CAST WEATHERPROOF 2 GANG COVER, GRAY

CA2GS | [Pass & Seymour](#)

### FEATURES & BENEFITS

Cast Weatherproof Cover 2 Gang 2 Toggles with 15A 120VAC Single Pole Toggle Switches, 4 Screw Mounting, Gray



- Broad line of two gang covers for switches, receptacles, GFCIs, and power outlets.
- Baked-on electrostatic, polyester, powder paint for superior scratch and corrosion resistance.
- Heavy-duty die-cast zinc.
- Stainless steel springs.
- All covers have 2 self-closing lids.
- Covers comply with 2005 NEC Section 406.8(A) and 406.8(B)(2).

### SPECIFICATIONS

#### GENERAL INFO

Color: Gray

Type: Covers

Special Features: Weatherproof

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No

CUL Listing No: No

cULus: No

cURus: No

Federal Spec: No

UL Listing No: No

UN SPSC: 39121305

UR: No

## DIMENSIONS

Height (US): 4.52"

Width (US): 4.58"

## TECHNICAL INFORMATION

Material: Cast

Capacity: 2-gang

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: INDIA

Buy American Act Status: No