

# Specifications

## Eaton CCP3023BC RS

Eaton Crouse-Hinds series PowerMate CCP plug, 30A, 0.390-1.375", Two-wire, three-pole, Style 2, Copper-free aluminum, Reverse service, 600 Vac/250 Vdc



Photo is representative

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series PowerMate CCP plug
<b>CATALOG NUMBER</b>	CCP3023BC RS
<b>UPC</b>	662276276857
<b>PRODUCT LENGTH/DEPTH</b>	6.5 in
<b>PRODUCT HEIGHT</b>	2.31 in
<b>PRODUCT WIDTH</b>	2.31 in
<b>PRODUCT WEIGHT</b>	2.2 lb



### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous
----------------------------	------------------------

### Product specifications

<b>AMPERAGE RATING</b>	30A
------------------------	-----

	Locations
<b>STANDARDS TYPE</b>	NEC/CEC
<b>NEMA RATING</b>	4X

<b>GROUNDING TYPE</b>	Style 2
<b>CONFIGURATION</b>	Two-wire, three-pole
<b>CABLE DIAMETER</b>	0.390-1.375"
<b>VOLTAGE RATING</b>	600 Vac/250 Vdc
<b>MATERIAL</b>	Copper-free aluminum
<b>SPECIAL FEATURES</b>	Reverse service

## Resources

<b>BROCHURES</b>	<a href="#">PowerMate Drilling Pin and Sleeve Devices brochure</a>
<b>CATALOGS</b>	<a href="#">PowerMate Drilling Pin and Sleeve Devices catalog page</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">PowerMate Drilling Pin and Sleeve Devices UL certification (Plugs and Connectors)</a> <a href="#">PowerMate Drilling Pin and Sleeve Devices cUL certification (Plugs and Connectors)</a>
<b>INSTALLATION INSTRUCTIONS</b>	<a href="#">IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices</a> <a href="#">IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">PowerMate Connectors</a> <a href="#">Eaton Specification Sheet - CCP3023BC RS</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

