


*Contractor Design*



**CD52W with BCD-5W**

Contractor Design in White  
shown with White blades.

**MODEL #CD52W BCD-5W**

<b>DIMENSIONS</b>	<b>SPECIFICATIONS</b>	<b>STANDARD OPERATION</b>
 <p>A-(2"DR)-10<sup>3</sup>/<sub>4</sub>" A-(4"DR)-12<sup>3</sup>/<sub>4</sub>" (DR-Down Rod)</p> <p>CD Fans are shipped with 2" and 4" down rods.</p>	<p>Blade Sweep – 52" # of Blades – 5 Blade Pitch – 12° Motor Size (MM) – 153 x 12 AMPS (HI Speed) – 0.5 Watts (HI Speed) – 60 RPM (HI/MED/LO) – 170/125/55 CFM (HI Speed) – 6300</p>	<p>Chain pull</p>
<p><b>WARRANTY</b> 30 Year Limited Lifetime Warranty</p>		



Better By Design

# The Contractor's Design Collection

Contractor's Design combines a lot of value for the money, and a stylish design.

- 5 BLADE, 52" BLADE SPAN WITH 12° PITCH
- LIGHT KIT ADAPTABLE
- HEAVY DUTY 153 X 12MM MOTOR
- TRIPLE CAPACITOR
- 13 BLADE FINISHES
- 7 POPULAR FAN FINISHES AVAILABLE
- TWO DOWNRODS SUPPLIED, 2" AND 4"
- 30-YEAR LIMITED WARRANTY
- 3-SPEED, REVERSIBLE



**CD52AW BCD-5AW**  
Antique White finish with Antique White blades.

• HI RES •  
• LO RES •



**CD52BN BCD-5BN**  
Brushed Nickel finish with Brushed Nickel blades.

• HI RES •  
• LO RES •



**CD52BS BCD5-WWB**  
Brownstone™ with Washed Walnut Birch blades.  
*(Brownstone™ is a registered trademark of Dolan Designs.)*

• HI RES •  
• LO RES •



**CD52EB BCD5-WB6**  
Antique White finish with Walnut Satin blades.

• HI RES •  
• LO RES •



**CD52PB BCD5-RW3**  
Polished Brass finish with Rosewood blades.

• HI RES •  
• LO RES •



**CD52W BCD-5W**  
White finish with White blades.

• HI RES •  
• LO RES •

*Note: Fans and Blades are Sold Separately.*

Craftmade International, Inc.

Contact Us

Product Support


# Contractor Design



## CD52W with BCD-5W

Contractor Design in White  
shown with White blades.

### MODEL #CD52W BCD-5W

DIMENSIONS	SPECIFICATIONS	STANDARD OPERATION
 <p>A-(2"DR)-10<sup>3</sup>/<sub>4</sub>" A-(4"DR)-12<sup>3</sup>/<sub>4</sub>" (DR-Down Rod)</p> <p>CD Fans are shipped with 2" and 4" down rods.</p>	<p>Blade Sweep – 52" # of Blades – 5 Blade Pitch – 12° Motor Size (MM) – 153 x 12 AMPS (HI Speed) – 0.5 Watts (HI Speed) – 60 RPM (HI/MED/LO) – 170/125/55 CFM (HI Speed) – 6300</p>	<p>Chain pull</p>
<p><b>WARRANTY</b> 30 Year Limited Lifetime Warranty</p>		



Better By Design

# The Contractor's Design Collection

Contractor's Design combines a lot of value for the money, and a stylish design.

- 5 BLADE, 52" BLADE SPAN WITH 12° PITCH
- LIGHT KIT ADAPTABLE
- HEAVY DUTY 153 X 12MM MOTOR
- TRIPLE CAPACITOR
- 13 BLADE FINISHES
- 7 POPULAR FAN FINISHES AVAILABLE
- TWO DOWNRODS SUPPLIED, 2" AND 4"
- 30-YEAR LIMITED WARRANTY
- 3-SPEED, REVERSIBLE



**CD52AW BCD-5AW**  
Antique White finish with Antique White blades.

• HI RES •  
• LO RES •



**CD52BN BCD-5BN**  
Brushed Nickel finish with Brushed Nickel blades.

• HI RES •  
• LO RES •



**CD52BS BCD5-WWB**  
Brownstone™ with Washed Walnut Birch blades.  
*(Brownstone™ is a registered trademark of Dolan Designs.)*

• HI RES •  
• LO RES •



**CD52EB BCD5-WB6**  
Antique White finish with Walnut Satin blades.

• HI RES •  
• LO RES •



**CD52PB BCD5-RW3**  
Polished Brass finish with Rosewood blades.

• HI RES •  
• LO RES •



**CD52W BCD-5W**  
White finish with White blades.

• HI RES •  
• LO RES •

*Note: Fans and Blades are Sold Separately.*

Craftmade International, Inc.

Contact Us

Product Support