



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CF42DTEIN835 42W 4 Pin Triple Tube Biax GX24Q-4 3500K Compact *Sylvania-Ledvance*

Catalog Number	CF42DTEIN835
Manufacturer	Sylvania-Ledvance
Description	Dulux 42W Triple Compact Fluorescent Amalgam Lamp With 4 Pin Base, 3500K Color Temperature, 82 Cri, For Use With Electronic and Dimming Ballasts, Ecologic
Weight per unit	0.2200 (lbs/each)
Product Category	Integrated Non-Ballasted Lamps

### Features

amperage rating	Ballast Dependent
average life	16000
Base	GX24Q-4;GX24q-4
Lamp Type	DULUX T/E
lumens	3,200
Shape	T4X3
start type	Electronic
total harmonic distortion	Ballast Dependent
Voltage	120.00 V
Voltage Rating	Ballast Dependent
Wattage	42

### Material, Color, and Finish

color rendering index (cri)	80
color temperature	3500
Finish	Phosphor Coated

### Descriptions

Description	42W 4 PIN TRIPLE TUBE BIAx GX24Q-4 3500K COMPACT
extra long description	SYL CF42DT/E/IN/835/ECO/20871 CF42D
Long Description	DULUX 42W triple compact fluorescent amalgam lamp with 4 pin base, 3500K color temperature, 82 CRI, for use with electronic and dimming ballasts, ECOLOGIC
Product Type	CF42DTEIN835ECO 50/CS 1/Sku

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135208713
Manufacturers Part Number	CF42DT/E/IN/835/ECO/20871
UPC	046135208713

### Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	Compact Fluorescent



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Availability

Status ..... Inactive .....

## Packaging

Carton ..... 1 .....

Package ..... 50 .....

Weight Per each ..... 0.22 .....

## Uses, Certifications, and Standards

Application ..... Commercial/Residential .....