

Specifications



Photo is representative

Eaton CCP2-1-100CF

Eaton Busmann series CCP UL98 fusible disconnect, 100A, UL98 fusible disconnect, Single-pole, 60 Hz, CUBEFuse, 200

General specifications

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton Busmann series CCP UL98 fusible disconnect |
| CATALOG NUMBER | CCP2-1-100CF |
| UPC | 051712709309 |
| PRODUCT LENGTH/DEPTH | 5.8 in |
| PRODUCT HEIGHT | 3.6 in |
| PRODUCT WIDTH | 1 in |
| PRODUCT WEIGHT | 0.52 lb |
| WARRANTY | Not Applicable |
| COMPLIANCES | RoHS Compliant |
| CERTIFICATIONS | UL 98 |



Electrical rating

AMPERAGE RATING 100A

Physical details

FUSE TYPE CUBEFuse

| | |
|-----------------------------|------------------|
| FREQUENCY RATING | 50/60 Hz |
| SHORT-CIRCUIT RATING | 200 kA |
| VOLTAGE RATING | 347 Vac, 125 Vdc |

| | |
|------------------------|-------------|
| NUMBER OF POLES | Single-pole |
|------------------------|-------------|

General information

SPECIAL FEATURES Finger Safe, 1/4" LOTO

Resources

CATALOGS

[Bussmann series complete full line catalog no. 1007](#)

[CCP2-1-100CF~1 Pole Comp Ckt Protect 100A](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - CCP2-1-100CF](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative

Eaton CCP2-1-100CF

Eaton Busmann series CCP UL98 fusible disconnect, 100A, UL98 fusible disconnect, Single-pole, 60 Hz, CUBEFuse, 200

General specifications

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton Busmann series CCP UL98 fusible disconnect |
| CATALOG NUMBER | CCP2-1-100CF |
| UPC | 051712709309 |
| PRODUCT LENGTH/DEPTH | 5.8 in |
| PRODUCT HEIGHT | 3.6 in |
| PRODUCT WIDTH | 1 in |
| PRODUCT WEIGHT | 0.52 lb |
| WARRANTY | Not Applicable |
| COMPLIANCES | RoHS Compliant |
| CERTIFICATIONS | UL 98 |



Electrical rating

AMPERAGE RATING 100A

Physical details

FUSE TYPE CUBEFuse

| | |
|-----------------------------|------------------|
| FREQUENCY RATING | 50/60 Hz |
| SHORT-CIRCUIT RATING | 200 kA |
| VOLTAGE RATING | 347 Vac, 125 Vdc |

| | |
|------------------------|-------------|
| NUMBER OF POLES | Single-pole |
|------------------------|-------------|

General information

SPECIAL FEATURES Finger Safe, 1/4" LOTO

Resources

CATALOGS

[Bussmann series complete full line catalog no. 1007](#)

[CCP2-1-100CF~1 Pole Comp Ckt Protect 100A](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - CCP2-1-100CF](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

