



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CFSR2023M15 20A, 125V RCPT *Crouse-Hinds*

Catalog Number	CFSR2023M15
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Powergard Replacement Receptacle, 20A, Two-Wire, Three-Pole, Copper-Free Aluminum, Single-Gang, M15 Model, 125 Vac
Weight per unit	1.9 (lbs/each)
Product Category	Pin & Sleeve Devices

Features

amperage rating	20
connection	Screws
dimensions	5.2500 IN X 4.3800 IN X 6.5000 IN
Phase	3
Poles	3
Voltage Rating	125V
Wire Size	#16-10 AWG

Dimensions and Weight

Size	3.24" x 5.70" x 3.37"
------	-----------------------

Descriptions

Description	20A, 125V RCPT
extra long description	CRS-H CFSR-2023-M15 REC DF 20A 125V
Features	Whether you are powering lighting fixtures or portable equipment, you need a receptacle solution that stands up to the harsh environmental and physical demands of land-based drilling applications. PowerGard receptacles and back boxes from Eaton's Crouse-Hinds Division meet and exceed your power needs with an easy-install, universal footprint suitable for rig maintenance, retrofits and new builds.
Long Description	Eaton Crouse-Hinds series PowerGard replacement receptacle, 20A, Two-wire, three-pole, Copper-free aluminum, Single-gang, M15 model, 125 Vac
Product Type	Rec DF 20A 125V PWRGD
Special Features	Haz Rated

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00662276515529
Manufacturers Part Number	CFSR-2023-M15
UPC	662276515529



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	Replacement receptacle

Packaging

Carton	1
Weight Per each	1.89

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Power Distribution and Control
environmental conditions	Wet locations
Mounting	Screw Mount
standard	ANSI/UL Standard 1010