

# Specifications



Photo is representative



## Eaton CHFEP120

Eaton CH GFCI circuit breaker, Ground fault equipment protector, Trip flag, 20 A, 10 kAIC, Single-pole, 120/240 V, CHFEP, Ground fault circuit interrupter, GFI, 30 mA

### General specifications

<b>PRODUCT NAME</b>	Eaton CH GFCI circuit breaker
<b>CATALOG NUMBER</b>	CHFEP120
<b>UPC</b>	786685627977
<b>PRODUCT LENGTH/DEPTH</b>	7.25 in
<b>PRODUCT HEIGHT</b>	6.5 in
<b>PRODUCT WIDTH</b>	6.75 in
<b>PRODUCT WEIGHT</b>	3.33 lb
<b>WARRANTY</b>	Limited lifetime
<b>CERTIFICATIONS</b>	UL 489
<b>CATALOG NOTES</b>	Switching Duty Rated, HACR Rated



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	Ground fault equipment protector
<b>SPECIAL FEATURES</b>	Trip flag
<b>AMPERAGE RATING</b>	20 A
<b>VOLTAGE RATING</b>	120/240 V
<b>CIRCUIT PROTECTION</b>	Ground fault circuit interrupter
<b>INDICATORS</b>	GFI
<b>PROTECTION</b>	30 mA
<b>INTERRUPT RATING</b>	10 kAIC
<b>MAIN CIRCUIT BREAKER</b>	CHFEP
<b>NUMBER OF POLES</b>	Single-pole

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Metering Products, Volume 1 Tab 4</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - CHFEP120</a>
<b>WARRANTY GUIDES</b>	<a href="#">Eaton type CH circuit breaker limited warranty June 2024</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



Photo is representative



## Eaton CHFEP120

Eaton CH GFCI circuit breaker, Ground fault equipment protector, Trip flag, 20 A, 10 kAIC, Single-pole, 120/240 V, CHFEP, Ground fault circuit interrupter, GFI, 30 mA

### General specifications

PRODUCT NAME	Eaton CH GFCI circuit breaker
CATALOG NUMBER	CHFEP120
UPC	786685627977
PRODUCT LENGTH/DEPTH	7.25 in
PRODUCT HEIGHT	6.5 in
PRODUCT WIDTH	6.75 in
PRODUCT WEIGHT	3.33 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL 489
CATALOG NOTES	Switching Duty Rated, HACR Rated



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	Ground fault equipment protector
<b>SPECIAL FEATURES</b>	Trip flag
<b>AMPERAGE RATING</b>	20 A
<b>VOLTAGE RATING</b>	120/240 V
<b>CIRCUIT PROTECTION</b>	Ground fault circuit interrupter
<b>INDICATORS</b>	GFI
<b>PROTECTION</b>	30 mA
<b>INTERRUPT RATING</b>	10 kAIC
<b>MAIN CIRCUIT BREAKER</b>	CHFEP
<b>NUMBER OF POLES</b>	Single-pole

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Metering Products, Volume 1 Tab 4</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - CHFEP120</a>
<b>WARRANTY GUIDES</b>	<a href="#">Eaton type CH circuit breaker limited warranty June 2024</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

