

Eaton CHFN120EP

Catalog Number: CHFN120EP

Eaton CH GFCI circuit breaker, CH Equipment Protection 30mA Breaker, 20A, Pigtail, 10 kAICkAIC

General specifications



Product Name
Eaton CH GFCI circuit breaker

Catalog Number
CHFN120EP

UPC
786689058869

Product Length/Depth
4.5 in

Product Height
3.25 in

Product Width
0.75 in

Product Weight
0.5 lb

Certifications
UL Listed

Photo is representative

Type

GFCI circuit breakers

Special features

30 mA breaker

Application

CH Equipment Protection 30mA Breaker, 20A, Pigtail, 10kAIC

Amperage Rating

20 A

Circuit breaker type

CH

Interrupt rating

10 kAIC

Connection

Pigtail

Number of poles

Single-pole

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - CHFN120EP](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton CHFN120EP

Catalog Number: CHFN120EP

Eaton CH GFCI circuit breaker, CH Equipment Protection 30mA Breaker, 20A, Pigtail, 10 kAICkAIC

General specifications



Product Name
Eaton CH GFCI circuit breaker

Catalog Number
CHFN120EP

UPC
786689058869

Product Length/Depth
4.5 in

Product Height
3.25 in

Product Width
0.75 in

Product Weight
0.5 lb

Certifications
UL Listed

Photo is representative

Type

GFCI circuit breakers

Special features

30 mA breaker

Application

CH Equipment Protection 30mA Breaker, 20A, Pigtail, 10kAIC

Amperage Rating

20 A

Circuit breaker type

CH

Interrupt rating

10 kAIC

Connection

Pigtail

Number of poles

Single-pole

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - CHFN120EP](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia