

# Eaton CH8NLJS

Catalog Number: CH8NLJS

Eaton CH Indoor Surface Cover, Surface cover, J, NEMA 1, CH, Surface, 0.75 in, CH32nlpn225j

## General specifications



Photo is representative

**Product Name**  
Eaton CH cover

**Catalog Number**  
CH8NLJS

**UPC**  
782116110384

**Product Length/Depth**  
34.1 in

**Product Height**  
1.1 in

**Product Width**  
14.3 in

**Product Weight**  
8.6 lb

**Warranty**  
Limited lifetime

**Certifications**  
Contact Manufacturer

**Catalog Notes**  
Designed for main lug only/convertible  
plug-on neutral loadcenters

## Product specifications

### Type

Cover

### Amperage Rating

400 A

### Bus material

Aluminum

### Mounting

Surface

### Phase

Three-phase

### Used with

Ch32nlpn225j

### Box size

J

### Enclosure

NEMA 1

### Interrupt rating

10 kAIC

## Resources

### Catalogs

Residential and Light Commercial, Load centers and Circuit Breakers, Volume 1 Tab 1

### Multimedia

AFCI Educational Video

### Specifications and datasheets

Eaton Specification Sheet - CH8NLJS

### Warranty guides

Eaton type CH circuit breaker limited warranty June 2024



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

# Eaton CH8NLJS

Catalog Number: CH8NLJS

Eaton CH Indoor Surface Cover, Surface cover, J, NEMA 1, CH, Surface, 0.75 in, CH32nlpn225j

## General specifications



Photo is representative

**Product Name**  
Eaton CH cover

**UPC**  
782116110384

**Product Height**  
1.1 in

**Product Weight**  
8.6 lb

**Certifications**  
Contact Manufacturer

**Catalog Number**  
CH8NLJS

**Product Length/Depth**  
34.1 in

**Product Width**  
14.3 in

**Warranty**  
Limited lifetime

**Catalog Notes**  
Designed for main lug only/convertible plug-on neutral loadcenters

## Product specifications

### Type

Cover

### Amperage Rating

400 A

### Bus material

Aluminum

### Mounting

Surface

### Phase

Three-phase

### Used with

Ch32nlpn225j

### Box size

J

### Enclosure

NEMA 1

### Interrupt rating

10 kAIC

## Resources

### Catalogs

Residential and Light Commercial, Load centers and Circuit Breakers, Volume 1 Tab 1

### Multimedia

AFCI Educational Video

### Specifications and datasheets

Eaton Specification Sheet - CH8NLJS

### Warranty guides

Eaton type CH circuit breaker limited warranty June 2024



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia