

Eaton CHP32L225X5

Catalog Number: CHP32L225X5

Eaton CH main lug loadcenters, PON, CH, 225A, X5, Copper, !, NEMA 1 indoor, Steel, 25 kAIC, 64, 32, 3, Single-phase, 120/240 V, #4 AWG-300 kcmil

General specifications

Product Name	Catalog Number
Eaton CH main lug loadcenter	CHP32L225X5
UPC	Product Length/Depth
786689054304	29 in
Product Height	Product Width
4 in	14.3 in
Product Weight	Certifications
15.8 lb	UL 67

Catalog Notes

Purchase Size X5 Cover Separately



defaultTaxonomyAttributeLabel

Special features

PON

Type

CH

Amperage Rating

225 A

Bus material

Copper

Number of circuits

64

Number of spaces

32

Phase

Single-phase

Voltage rating

120/240 V

Box size

X5

Enclosure

NEMA 1

Enclosure material

Steel

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

Loadcenters and Circuit Breakers

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CHP32L225X5

Warranty guides

Eaton type CH circuit breaker limited warranty June 2024



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton CHP32L225X5

Catalog Number: CHP32L225X5

Eaton CH main lug loadcenters, PON, CH, 225A, X5, Copper, !, NEMA 1 indoor, Steel, 25 kAIC, 64, 32, 3, Single-phase, 120/240 V, #4 AWG-300 kcmil

General specifications

Product Name	Catalog Number
Eaton CH main lug loadcenter	CHP32L225X5
UPC	Product Length/Depth
786689054304	29 in
Product Height	Product Width
4 in	14.3 in
Product Weight	Certifications
15.8 lb	UL 67

Catalog Notes

Purchase Size X5 Cover Separately



defaultTaxonomyAttributeLabel

Special features

PON

Type

CH

Amperage Rating

225 A

Bus material

Copper

Number of circuits

64

Number of spaces

32

Phase

Single-phase

Voltage rating

120/240 V

Box size

X5

Enclosure

NEMA 1

Enclosure material

Steel

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP32L225X5](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)