



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

CHP42B200R CH Pon Loadcntr 200A Main BRKR 42 Space N3R

Eaton Corp

Catalog Number	CHP42B200R
Manufacturer	Eaton Corp
Description	Eaton CH Main Breaker Loadcenters, Cover Included, Main Breaker, 200 A, X7, Copper, Nema 3R, Metallic, CSR, 84, 42, Three-Wire, Single-Phase, Overhead, 120/240 V
Weight per unit	33.0 (lbs/each)
Product Category	Single Phase Main Breaker Load

Features

amperage rating	200
media	Yes
number of spaces	42
Phase	1
Voltage Rating	120/240 V

Dimensions and Weight

Depth	37
Height	5.19
Size	X7
Width	14.31

Descriptions

Description	CH PON LOADCNTR 200A MAIN BRKR 42 SPACE N3R
extra long description	ETN CHP42B200R CH PON LC, 200A, MB,
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH main breaker loadcenters,Cover included,Main breaker,200 A,X7,Copper,NEMA 3R,Metallic,CSR,84,42,Three-wire,Single-phase,Overhead,120/240 V
Product Type	CH Pon LC, 200A, MB, 42SP, N3R
Special Features	Cover included



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Eaton
GTIN	00786689058715
Manufacturers Part Number	CHP42B200R
UPC	786689058715

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
Type	Main breaker loadcenter

Packaging

Carton	1
Weight Per each	33

Uses, Certifications, and Standards

Application	Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other
standard	UL 50,UL 67