



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHPX7BFSPRK Eaton CH Indoor Main Breaker Cover- Logo MR Sparky

Eaton Corp

Catalog Number	CHPX7BFSPRK
Manufacturer	Eaton Corp
Description	Eaton CH Indoor Main Breaker Cover- Logo MR Sparky, Flush-Mount Applications, 225 A, X7, White, Nema 1, Flush, 42 Spaces, Plug On Neutral, CH Breakers
Weight per unit	12.8 (lbs/each)
Product Category	Distribution Equipment

Features

dimensions	1.0000 IN X 15.3100 IN X 38.0000 IN
media	Yes

Descriptions

Description	EATON CH INDOOR MAIN BREAKER COVER- LOGO MR SPARKY
extra long description	ETN CHPX7BFSPRK CONTRACTOR BRANDED
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH Indoor Main Breaker Cover- Logo Mr Sparky, Flush-mount applications, 225 A, X7, White, NEMA 1, Flush, 42 Spaces, Plug On Neutral, CH Breakers
Product Type	Contractor Branded Size X7 CVR For CH LC

Manufacturer Information

Brand	Eaton
GTIN	00786689728601
Manufacturers Part Number	CHPX7BFSPRK
UPC	786689728601

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Accessory

Packaging

Carton	1
Weight Per each	12.8



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Residential Bldgs & Facilities - Residential Bldgs & Facilities -
Other Residential Bldgs & Facilities - Residential Bldgs/Facilities -
Aftermarket

standard

Contact Manufacturer