



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHP08N200RF CH Pon Loadcncr 200A Convertible 8 Space N3R

Eaton Corp

Catalog Number	CHP08N200RF
Manufacturer	Eaton Corp
Description	Eaton CH Convertible Loadcenters, Cover Included, Convertible (Main Device Purchased Separately), 200 A, X5, Copper, Nema 3R, Metallic, CSR, 16, 8, Three-Wire, Single-Phase, Overhead
Weight per unit	27.0 (lbs/each)
Product Category	Single Phase Convertible Load

Features

amperage rating	200
media	Yes
number of spaces	8
Phase	1

Dimensions and Weight

Depth	29
Height	5.19
Size	X5
Width	14.31

Descriptions

Description	CH PON LOADCNCR 200A CONVERTIBLE 8 SPACE N3R
extra long description	ETN CHP08N200RF CH PON Loadcenter,
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH convertible loadcenters, Cover included, Convertible (main device purchased separately), 200 A, X5,Copper, NEMA 3R, Metallic, CSR, 16, 8, Three-wire, Single-phase, Overhead
Product Type	CH Pon Loadcenter, 200A, Conv, 8SP, N3R
Special Features	Cover included

Manufacturer Information

Brand	Eaton
GTIN	00786689058487
Manufacturers Part Number	CHP08N200RF
UPC	786689058487



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LOADCENTERS & COVERS

Type Convertible loadcenter

Packaging

Carton 1

Weight Per each 27

Uses, Certifications, and Standards

Application Residential Bldgs & Facilities - Residential Bldgs & Facilities -

..... Other

standard UL 50,UL 67