



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CHU7N7N5GS Unmetered Surf Pop (2) 5-20R2GFI (1) 6-20R2

Eaton Corp

Catalog Number	CHU7N7N5GS
Manufacturer	Eaton Corp
Description	Eaton Pedestal Mount Unmetered, Unmetered, 20A, 20A, 20A, Non-Ground Fault, Non-Ground Fault, Ground Fault, Top, Surface, Circuits: 4, Nema 5-20R2GFI, Nema 5-20R2GFI, Nema 6-20R2, 3, 3, 3, 125V, 125V, 250V
Weight per unit	26.0 (lbs/each)
Product Category	Unmetered Power Outlet Panels

### Dimensions and Weight

Depth	4.3
Height	17.1
Width	9.5

### Descriptions

Description	UNMETERED SURF POP (2) 5-20R2GFI (1) 6-20R2
extra long description	ETN CHU7N7N5GS UM SURF POP (2) 5-20
Features	Eaton's temporary power panels provide safe, reliable power for RV and construction sites. Durable, long-lasting units are available as metered (ring or ringless) or unmetered and can be mounted at the surface, on a pedestal, or in a back-to-back configuration.
Long Description	Eaton pedestal mount unmetered, Unmetered, 20A, 20A, 20A, Non-ground fault, Non-ground fault, Ground fault, Top, Surface, Circuits: 4, NEMA 5-20R2GFI, NEMA 5-20R2GFI, NEMA 6-20R2, 3, 3, 3, 125V, 125V, 250V
Product Type	Um Surf Pop (2) 5-20R2GFI (1) 6-20R2

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782114215753
Manufacturers Part Number	CHU7N7N5GS
UPC	782114215753

### Taxonomies, Classifications, and Categories

Category Description	RV Power Pedestals
Type	Pedestal mount unmetered

### Availability

Status	Inactive
--------	----------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	26

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting	SURFACE
standard	UL Listed file E163588,UL 231