



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CL710 Acdc Auto-Ranging Pro Clamp Meter

Klein Tools

Catalog Number	CL710
Manufacturer	Klein Tools
Description	Klein Tools CL710 Clamp Meter Delivers Accurate Measurements Across Ac/DC Current, Voltage, Resistance, Continuity, Frequency, and Capacitance, All With True RMS Precision. It Features Diode Testing and A Low Impedance (Loz) Mode to Eliminate Ghost Voltages. The Clamp Features NCV Detection With Escalating Audio-Visual Alerts The Closer to The Voltage Source. The Transflective Reverse-Contrast Display and Lighted Dial Ensure Visibility In Any Lighting A Reliable Tool For Diverse Applications.
Weight per unit	0.7370 (lbs/each)
Product Category	Tools & Testers

Features

ac voltage	1000V
Accuracy	See Instructions
auto ranging	Yes
auto-power off	Yes
Capacitance	6000 μ F
display	Transflective Reverse-Contrast with 6000 Count LCD
functions	AC/DC Voltage, AC/DC Current, Resistance, Audible Continuity, Low Impedance, Non-Contact Voltage Testing, Diode Test, Capacitance, Frequency/Duty Cycle, Min/Max Value, Rel/Zero, Data Hold Capability
included	Clamp Meter; Right-Angle Input Test Leads; Storage Pouch; Instruction Manual; and 3 x AAA Batteries
Material	ABS/Electronics
Overall Height	1.65" (4.2 cm)
Overall Width	3.47" (8.8 cm)
Temperature Range	-
Voltage	1000V AC; 1000V DC

Dimensions and Weight

Overall Length	9.06" (2.30 cm)
----------------	-----------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	ACDC AUTO-RANGING PRO CLAMP METER
extra long description	KLEIN CL710 600A AC/DC Digital Pro
Long Description	Klein Tools CL710 Clamp Meter delivers accurate measurements across AC/DC current, voltage, resistance, continuity, frequency, and capacitance, all with True RMS precision. It features diode testing and a Low Impedance (LoZ) mode to eliminate ghost voltages. The clamp features NCV detection with escalating audio-visual alerts the closer to the voltage source. The transfective reverse-contrast display and lighted dial ensure visibility in any lighting a reliable tool for diverse applications.
Product Type	600A Ac/DC Digital Pro Clamp Meter
Special Features	Transflective Reverse-Contract Display; Lighted Dial; Built-in Lead Holder

Manufacturer Information

Brand	Klein Tools
GTIN	00092644694493
Manufacturers Part Number	CL710
UPC	092644694493

Taxonomies, Classifications, and Categories

Category Description	TEST EQUIPMENT, TESTERS AND MULTIMETERS
Type	Pro Clamp Meter

Packaging

Carton	1
Weight	13 oz (369 g) Including Batteries
Weight Per each	0.737

Uses, Certifications, and Standards

Application	Variety of electrical diagnostic and troubleshooting applications
standard	CAT IV 600V, CAT III 1000V, Class 2, Double Insulation, CE, UKCA