




ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CLT50FC20 Loom Tubing *Panduit Corporation*

| | |
|------------------|---|
| Catalog Number | CLT50FC20 |
| Manufacturer | Panduit Corporation |
| Description | The CLT50F-C20 Polyethylene Corrugated Loom Tubing Protects Cables From Impact and Abrasion. Features A Slit For Easy Installation Onto A Bundle Of Wires or A Pre-Assembled Harness Assembly, Increasing Productivity. Hold In Place With Cable Ties and Accessories. Suitable For Indoor Applications. UL94-HB Flammability Rating and A Maximum Temperature Rating Of 122°F (50°C). Polyethylene. Inside Diameter 0.51" (13 MM). Color Black. 1 Per Package. |
| Weight per unit | 4.0 (lbs/each) |
| Product Category | Cable Ties & Wraps |

Features

| | |
|------------------|--------------|
| Inside Diameter | 0.518 |
| Material | Polyethylene |
| media | Yes |
| outside diameter | 0.67 |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Black |
|-------|-------|

Dimensions and Weight

| | |
|--------|-----|
| Length | 100 |
|--------|-----|

Descriptions

| | |
|------------------------|---|
| Description | LOOM TUBING |
| extra long description | PAN CLT50F-C20 CLT50F-C20 Loom Tubi |
| Long Description | The CLT50F-C20 Polyethylene Corrugated Loom Tubing protects cables from impact and abrasion. Features a slit for easy installation onto a bundle of wires or a pre-assembled harness assembly, increasing productivity. Hold in place with cable ties and accessories. Suitable for indoor applications. UL94-HB flammability rating and a maximum temperature rating of 122°F (50°C). Polyethylene. Inside diameter 0.51" (13 mm). Color Black. 1 per package. |
| Product Type | CLT50F-C20 Loom Tubing, Black, Pe, 0.5" Nom Dia., 100', PK1 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | PANDUIT |
| GTIN | 00074983287123 |
| Manufacturers Part Number | CLT50F-C20 |
| UPC | 074983287123 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | HEAT/COLD SHRINK |
| Type | Corrugated Loom Tubing |

Packaging

| | |
|-----------------|----|
| Carton | 10 |
| Package | 4 |
| Weight Per each | 4 |

Uses, Certifications, and Standards

| | |
|--------------------|--|
| Application | Covers wire and cable to protect from abrasion |
| standard | RoHS Compliant |
| Temperature Rating | 122 |