

Eaton CMB1212P200BTS

Catalog Number: CMB1212P200BTS

Eaton resi meter breaker, All-in-ones, 200 A, C, Copper, NEMA 3R, Bottom and top, #6-350 kcm#6-350 kcmProvisions, Surface mounting, 12, Four-jaw, 1, 12, Single-phase, Ringless, Type CH breakers, 120/240 Vac

General specifications

Product Name	Catalog Number
Eaton residential meter breaker	CMB1212P200BTS
UPC	Product Length/Depth
782114858554	5.38 in
Product Height	Product Width
32.38 in	14.44 in
Product Weight	Warranty
42 lb	Limited lifetime
Certifications	
UL Listed	



Product specifications

Interrupt rating

10 kAIC

Utility approvals

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

Phase

Single-phase

Ground

#6-350 kcmil

Bus material

Copper

Number of jaws

Four-jaw

Main circuit breaker

Provisions

Enclosure

NEMA 3R

Type

All-in-ones

Feed type

Top/bottom

Number of sockets

1

Used with

Type CH breakers

Voltage rating

120/240 V

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - METER BREAKER EAST COAST STYLE (PROVISION)

Specifications and datasheets

Eaton Specification Sheet - CMB1212P200BTS

Technical Data Residential Meter Breakers: Type CH and BR Residential

Number of circuits

12

Box size

C



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)