



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHU602G2GKGSX Pop Unmetered Sur 6CKT 60A Main 20/20/20

Eaton Corp

Catalog Number	CHU602G2GKGSX
Manufacturer	Eaton Corp
Description	Eaton Pedestal Mount Unmetered, Unmetered, 60A Main, 20A, 20A, 20A, Ground Fault, Ground Fault, Ground Fault, Top, Surface, Circuits: 6, Nema 5-20R2 WR, Nema 5-20R2 WR, Nema 6-20R2 WR, 3, 3, 3, 125V, 125V, 250V
Weight per unit	16.0 (lbs/each)
Product Category	Distribution Equipment

Features

dimensions	6.8000 IN X 9.5000 IN X 7.6000 IN
------------	-----------------------------------

Dimensions and Weight

Depth	6.8000
Height	7.6000
Width	9.5000

Descriptions

Description	POP UNMETERED SUR 6CKT 60A MAIN 20/20/20
extra long description	ETN CHU602G2GKGSX POP UNMETERED SUR
Features	Eaton's temporary power panels provide safe, reliable power for RV and construction sites. Durable, long-lasting units are available as metered (ring or ringless) or unmetered and can be mounted at the surface, on a pedestal, or in a back-to-back configuration.
Long Description	Eaton pedestal mount unmetered, Unmetered, 60A Main, 20A, 20A, 20A, Ground fault, Ground fault, Ground fault, Top, Surface, Circuits: 6, NEMA 5-20R2 WR, NEMA 5-20R2 WR, NEMA 6-20R2 WR, 3, 3, 3, 125V, 125V, 250V
Product Type	Pop Unmetered Sur 6CKT 60A Main 20/20/20

Manufacturer Information

Brand	Eaton
GTIN	00786689528294
Manufacturers Part Number	CHU602G2GKGSX
UPC	786689528294

Taxonomies, Classifications, and Categories

Category Description	RV Power Pedestals
Type	Pedestal mount unmetered

Packaging

Carton	1
Weight Per each	16



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels
and OEMs

Mounting
standard

SURFACE
UL Listed