



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

700 York Ave.
67401-0000, KS Salina
Phone: 785-914-5431
Fax: 785-914-5432



CIRS Led Single Remote Head White *Hubbell Lighting/Current Hli*

Catalog Number	CIRS
Manufacturer	Hubbell Lighting/Current Hli
Description	N/A, Mounting Type: Wall, Ceiling, End Mount, Face Style: Universal Single/Double Face, Wording On Sign: Exit, Letter Color: Red, Color: White, Number Of Lamps: 0, Operation: Emergency Operation, Battery Type: Lead-Calcium, Battery Runtime: 90 Min, Voltage Rating: 120/277 Vac.
Weight per unit	1.0 (lbs/each)
Product Category	Emergency Lighting, Exit Signs

Features

battery	Lead-Calcium
exact weight	1
Fixture Type	Emergency Lighting
Lamp Type	none
Lamp Wattage	4.5
Number of Lamps	0
Voltage Rating	120/277
Wattage	4.5

Material, Color, and Finish

Color	White
housing color	White
Letter Color	RED

Dimensions and Weight

Size	6.7 Inch W x 2.5 Inch D x 4.7 Inch H
------	--------------------------------------

Descriptions

Description	LED SINGLE REMOTE HEAD WHITE
extra long description	
Long Description	N/A, Mounting Type: Wall, ceiling, end mount, Face style: Universal Single/Double Face, Wording On Sign: EXIT, Letter Color: Red, Color: White, Number of Lamps: 0, Operation: emergency operation, Battery Type: Lead-Calcium, Battery Runtime: 90 min, Voltage Rating: 120/277 VAC.
Product Type	Emergency Remote Head



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

700 York Ave.
67401-0000, KS Salina
Phone: 785-914-5431
Fax: 785-914-5432

Manufacturer Information

Brand	COMPASS
GTIN	00782520862022
Manufacturers Part Number	CIRS
UPC	782520862022

Taxonomies, Classifications, and Categories

Category Description	Emergency Lighting
	Emergency Lighting, Exit Signs & Inverters
Type	Single Remote Head

Packaging

Carton	1
Weight Per each	1

Uses, Certifications, and Standards

Application	Manufacturing;Warehouse;Offices;Hospitality;Quick Service Restaurants;Retail;Automotive Dealers;Educational;Healthcare
Mounting standard	Wall, ceiling, end mount UL 924 Listed