



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CR20RED Duplex Recp 20A/125V Side Wire RD

*Pass & Seymour/Legrand*

Catalog Number	CR20RED
Manufacturer	Pass & Seymour/Legrand
Description	Commercial Spec Grade Duplex Receptacle, Side Wire 20A 125V
Weight per unit	0.1962 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	20
connection	Side wire
Dielectric Strength	Withstands 1500V minimum
indoor/outdoor	Indoor
Material	Nylon
Number of Wires	3
Outlet Type	Indoor, Commercial
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Height	3.281
Width	.780

### Descriptions

Description	DUPLEX RECP 20A/125V SIDE WIRE RD
extra long description	P&S CR20RED RECP DUP 20A/125V SIDE
Long Description	Commercial Spec Grade Duplex Receptacle, Side Wire 20A 125V
Product Type	Recep Dup 20A/125V Side Wire Red
Special Features	Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly. .032 inch thick, brass, triple-wipe power contacts for lasting retention. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant nylon face and thermoplastic back body. Accepts #14 - #10 AWG solid or stranded copper or copper-clad wire. Terminal compartments isolated from each other for positive conductor containment. Tri-drive termina



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007180145
Manufacturers Part Number	CR20-RED
UPC	785007180145

## Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Outlet

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	10
Package	100
Weight Per each	0.1962

## Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-20R
standard	CULUS, UL498, CSA C22.2 No. 42