



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CSB20AC2I 20A 120/277VAC B+S Wire Comm DP SW Iv *Pass & Seymour/Legrand*

| | |
|------------------|--|
| Catalog Number | CSB20AC2I |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Toggle Switch, 2 Poles, 20 A, 120/277 V Ac, Nylon Material, Silver Cadmium Oxide Contact Material, Ivory, Grounding Connection, Wall Mount, 1.320 (L) X 1.073 (W) X 3.281 (H) In, -40 °C Operating Temperature, +115 °C Operating Temperature, 0.19 LB |
| Weight per unit | 0.1872 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|-----------------|---------------------|
| action | Double pole |
| amperage rating | 20 |
| Contact Rating | 20 Amp, 120/277 VAC |
| insulation | False |
| Poles | 2 |
| Switch Type | Toggle |
| Voltage | 120.0 V |
| Wire Size | #14 - #10 Awg |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|------|--------|
| Size | 3.3 in |
|------|--------|

Descriptions

| | |
|------------------------|--------------------------------------|
| Description | 20A 120/277VAC B+S WIRE COMM DP SW I |
| extra long description | P&S CSB20AC2I 20A 120/277VAC B+S WI |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007126174 |
| Manufacturers Part Number | CSB20AC2I |
| UPC | 785007126174 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | Industrial receptacles |
| Type | TOGGLE SWITCH |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|--------|
| Carton | 10 |
| Package | 50 |
| Weight Per each | 0.1872 |

Uses, Certifications, and Standards

| | |
|----------------------|--|
| Enclosure | Nylon |
| Mounting standard | WALL FEDSPEC, CULUS, UL 498/20, FEDSPEC |