



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CSB20AC3I 20A 120/277VAC B+S Wire Comm 3W SW Iv

Pass & Seymour/Legrand

Catalog Number	CSB20AC3I
Manufacturer	Pass & Seymour/Legrand
Description	Construction 3-Way Switch, Back and Side-Wire, 20A 120/277V. These Switches Offer Excellent Value While Meeting Federal Specification Standards. External Screw-Pressure-Plate Back Wiring Enables Fast Installation and Superior Electrical Connections. Rugged Construction Shrugs Off Hard Use and Abuse.
Weight per unit	0.1893 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	Three pole
amperage rating	20
connection	Side Wire or external screw-pressure plate
Connection Type	Wired
Contact Configuration	One piece brass alloy contact arm
Contact Rating	Oversized silver alloy contacts
Degree of Protection	1500V Dielectric Withstand Voltage
indoor/outdoor	Indoor
insulation	False
Material	Thermoplastic
Poles	3-way
Switch Type	Toggle
Voltage	120/277 V
Voltage Rating	120/277
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3 in
------	--------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	20A 120/277VAC B+S WIRE COMM 3W SW IV
extra long description	P&S CSB20AC3I 20A 120/277VAC B+S WI
Long Description	Construction 3-Way Switch, Back and Side-Wire, 20A 120/277V. These switches offer excellent value while meeting federal specification standards. External screw-pressure-plate back wiring enables fast installation and superior electrical connections. Rugged construction shrugs off hard use and abuse.
Product Type	20A 120/277VAC B+S Wire Comm 3W SW I
Special Features	Back & side wire, locking support, heavy duty toggle

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007126273
Manufacturers Part Number	CSB20AC3-I
UPC	785007126273

Taxonomies, Classifications, and Categories

Category Description	Industrial receptacles
Type	SWITCH

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	10
Package	50
Weight Per each	0.1893

Uses, Certifications, and Standards

Application	Commercial
Enclosure	Nylon
Mounting	WALL
nema rating	WD-1 and WD-6
standard	FEDSPEC, CULUS, UL Listed E140597, Standard UL20, FedSpec WS896, Flammability Rating UL94 V2, FEDSPEC