



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CSVTL485000LMMV0 4' 34W 120-277V 4K 80CRI Vaportight Led Strip

Lithonia Lighting - Acuity

Catalog Number	CSVTL485000LMMV0
Manufacturer	Lithonia Lighting - Acuity
Description	The CSVT By Lithonia Lighting Is Built On The Technological Framework Of The CSS, Providing Greater Customization and Performance For Everyday Spaces. and With The Ability to Switch Lumens and Adjust Color Temperature In One Fixture, The CSVT Can Easily Be Adapted to The Needs Of Each Project – 9 Different Variations Within The Same Sku!
Weight per unit	5.2 (lbs/each)
Product Category	Lighting

Features

average life	54
dimensions	50.3 x 5.4 x 3.8
Fixture Type	Low Bay
Hardware	No
Lamp Included	Yes
Lamp Type	LED - Static
lumens	5000
Material	Polycarbonate
Power Source	Hardwired
Shape	Rectangular
Voltage Rating	120-277
Warranty	5
Wattage	47.6

Material, Color, and Finish

Color	Gray
Lens Color	WHITE
Lens Material	Polycarbonate
Style	Traditional

Dimensions and Weight

Height	3.8
Length	50.3
Size	50.3x5.4x3.8 IN
Width	5.4



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Construction	New Construction,Remodel
Description	4' 34W 120-277V 4K 80CRI VAPORTIGHT LED STRIP
extra long description	LITH CSVT L48 5000LM MVOLT 40K 80CR
Features	Contractor Select
Long Description	The CSVT by Lithonia Lighting is built on the technological framework of the CSS, providing greater customization and performance for everyday spaces. And with the ability to switch lumens and adjust color temperature in one fixture, the CSVT can easily be adapted to the needs of each project – 9 different variations within the same SKU!
Product Type	Low Bay

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00194995069408
Manufacturers Part Number	CSVT L48 5000LM MVOLT 40K 80CR
UPC	194995069408

Taxonomies, Classifications, and Categories

Category Description	LED HAZARDOUS LOCATION & VAPOR TIGHT LIGHTING
Type	LOW BAY

Trade Size

aperture size	4FT
---------------	-----

Packaging

Carton	1
Weight Per each	5.2

Uses, Certifications, and Standards

Application	Manufacturing,Parking Garage,Sports and Recreation,Warehouses
environmental conditions	Demanding,Indoor,Outdoor
Mounting	Pendant,Surface,Suspended
standard	CSA,NOMDLC Standard