



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

CSVTL48AL03MVOLT 4' Lumen and CCT Selectable Led Vaportight

Lithonia Lighting - Acuity

| | |
|------------------|--|
| Catalog Number | CSVTL48AL03MVOLT |
| Manufacturer | Lithonia Lighting - Acuity |
| Description | The CSVT™ Vapor Tight Led Strip Light By Lithonia Lighting Is Built On The Technological Framework Of The CSS and Uses A Tongue & Groove, Poured In Gasket Design, Allowing For Easy, On The Go Maintenance and Provides For Impressive Ratings Such As Csa Wet Location, IP65, IP66 For General Washdown, and NEMA4X! |
| Weight per unit | 5.2 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|----------------|------------------------------|
| average life | 60 |
| dimensions | 50.3 x 5.4 x 3.8 |
| Fixture Type | Low Bay |
| Hardware | No |
| Lamp Included | Yes |
| Lamp Type | LED - Static |
| lumens | 3000 ,4000 ,5000 ,Switchable |
| Material | Polycarbonate |
| Power Source | Hardwired |
| Shape | Rectangular |
| Voltage Rating | 120-277 |
| Warranty | 5 |
| Wattage | 47.6 |

Material, Color, and Finish

| | |
|---------------|---------------|
| Color | Gray |
| Lens Color | WHITE |
| Lens Material | Polycarbonate |
| Style | Traditional |

Dimensions and Weight

| | |
|--------|------|
| Height | 3.8 |
| Length | 50.3 |
| Width | 5.4 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|--|
| Construction | New Construction,Remodel |
| Description | 4' LUMEN AND CCT SELECTABLE LED VAPORTIGHT |
| extra long description | LITH CSVT L48 ALO3 MVOLT SWW3 80CRI |
| Features | Contractor Select |
| Long Description | The CSVT™ Vapor Tight LED Strip Light by Lithonia Lighting is built on the technological framework of the CSS and uses a tongue & groove, poured in gasket design, allowing for easy, on the go maintenanceand provides for impressive ratings such as CSA wet location,IP65, IP66 for general washdown, and NEMA4X! |
| Product Type | Low Bay |

Manufacturer Information

| | |
|---------------------------|--------------------------------|
| Brand | Lithonia Lighting |
| GTIN | 00194995069507 |
| Manufacturers Part Number | CSVT L48 ALO3 MVOLT SWW3 80CRI |
| UPC | 194995069507 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | LED HAZARDOUS LOCATION & VAPOR TIGHT LIGHTING |
| Type | LOW BAY |

Trade Size

| | |
|---------------|-----|
| aperture size | 4FT |
|---------------|-----|

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 5.2 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Manufacturing,Parking Garage,Sports and Recreation,Warehouses |
| environmental conditions | Demanding,Indoor,Outdoor |
| Mounting | Pendant,Surface,Suspended |
| standard | CSA,NOMDLC Standard |