



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



D2138NE Lineman'S Pliers, High-Leverage, 8"

Klein Tools

Catalog Number	D2138NE
Manufacturer	Klein Tools
Description	The Klein Tools 8-Inch Side-Cutting Pliers Offer A High-Leverage Design Ideal For Cutting A Wide Variety Of Cable and Wire Sizes. These Pliers Are Crafted From Steel Alloy For Strength and Offer Knurled Jaws For A Sure Grip.
Weight per unit	0.9000 (lbs/each)
Product Category	Pliers, Wrenches, Saw, Pouches

Features

Handle Length	4.84" (12.3 cm)
Jaw Length	1.438" (3.7 cm)
jaw thickness	0.625" (1.6 cm)
Jaw Width	1.21" (3.1 cm)
knife length	0.719" (1.8 cm)
Material	Steel
media	Yes
tether capable	No

Material, Color, and Finish

Handle Color	dark blue
--------------	-----------

Dimensions and Weight

Overall Length	8.59" (21.8 cm)
----------------	-----------------

Descriptions

Description	LINEMAN'S PLIERS, HIGH-LEVERAGE, 8"
extra long description	KLEIN D213-8NE High Lev. Pliers, S
Features	The Klein Tools 8-Inch Side-Cutting Pliers offer a high-leverage design ideal for cutting a wide variety of cable and wire sizes. These pliers are crafted from steel alloy for strength and offer knurled jaws for a sure grip.
Long Description	The Klein Tools 8-Inch Side-Cutting Pliers offer a high-leverage design ideal for cutting a wide variety of cable and wire sizes. These pliers are crafted from steel alloy for strength and offer knurled jaws for a sure grip.
Product Type	High Lev. Pliers, Side Cut, Ne, 8"



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Klein Tools
GTIN	00092644700323
Manufacturers Part Number	D213-8NE
UPC	092644700323

Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	Side Cutting Pliers

Packaging

Carton	1
Package	6
Weight	14.4 oz (408 g)
Weight Per each	0.9

Uses, Certifications, and Standards

standard	Y
----------	---