



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## D2288INS Diagonal Cutting Pliers Insulated High Leverage 8"

*Klein Tools*

Catalog Number	D2288INS
Manufacturer	Klein Tools
Description	These High-Leverage Insulated Diagonal-Cutting Pliers Are 1000V Rated For Safety On The Job. The Thick, Exceptionally Tough White Inner Layer Coating Is Bonded To The Tool. Integral Thumb Guards Prevent Hand Contact With Conductive Parts. The Bright Orange Handles Make This Tool Comfortable to Use All Day and Easy to Identify In The Field. The Durable, Molded Insulation Meets or Exceeds IEC 60900 and Astm F1505 Standards For Insulated Tools. Cutting Knives Are Induction Hardened For Long Life.
Weight per unit	0.8400 (lbs/each)
Product Category	Pliers, Wrenches, Saw, Pouches

### Features

Handle Length	4.9" (12.4 cm)
Jaw Length	0.781" (2 cm)
jaw thickness	0.46" (1.2 cm)
Jaw Width	1.25" (3.2 cm)
knife length	0.188 (0.5 cm)MaterialSteelOverall Length4.25 (10.8 cm)
Material	Induction Hardened Steel
media	Yes
tether capable	No

### Material, Color, and Finish

Handle Color	ORANGE
--------------	--------

### Dimensions and Weight

Overall Length	8.24" (20.9 cm)
----------------	-----------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	DIAGONAL CUTTING PLIERS INSULATED HIGH LEVERAGE 8"
extra long description	KLEIN D228-8-INS 8" Insulated, Diag
Features	These High-Leverage Insulated Diagonal-Cutting pliers are 1000V rated for safety on the job. The thick, exceptionally tough white inner layer coating is bonded to the tool. Integral thumb guards prevent hand contact with conductive parts. The bright orange handles make this tool comfortable to use all day and easy to identify in the field. The durable, molded insulation meets or exceeds IEC 60900 and ASTM F1505 standards for insulated tools. Cutting knives are induction hardened for long life.
Long Description	These High-Leverage Insulated Diagonal-Cutting pliers are 1000V rated for safety on the job. The thick, exceptionally tough white inner layer coating is bonded to the tool. Integral thumb guards prevent hand contact with conductive parts. The bright orange handles make this tool comfortable to use all day and easy to identify in the field. The durable, molded insulation meets or exceeds IEC 60900 and ASTM F1505 standards for insulated tools. Cutting knives are induction hardened for long life.
Product Type	8" Insulated, Diagonal-Cutters
Special Features	Flame Retardant and Impact Resistant Handle

## Manufacturer Information

Brand	Klein Tools
GTIN	00092644720420
Manufacturers Part Number	D228-8-INS
UPC	092644720420

## Taxonomies, Classifications, and Categories

Category Description	WIRE LUBE, MARKERS, & TIES
Type	Diagonal Cutting Pliers

## Packaging

Carton	1
Package	3
Weight	11.2 oz (318 g)
Weight Per each	0.84

## Uses, Certifications, and Standards

Application	ACSR, Screws, Nails and Most Hardened Wire
Configuration	Tapered Nose
standard	IEC 60900 and ASTM F1505