



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DG132061FNC21C DG1 230V FR4 N1 20HP 61A CT 25HP 75A VT

Eaton Corp

Catalog Number	DG132061FNC21C
Manufacturer	Eaton Corp
Description	Eaton Powerxl DG1 Variable Frequency Drive, 208-240V Input 15 KW 20 HP CT 3PH 50/60 HZ 61A Output IP21/Type 1 Enclosure FR4 LCD Internal Emc Filter and DC Choke Ethernet, RS-485, Bacnet MS/TP, Modbus TCP and Rtu Ports 2 Exp Slots
Weight per unit	80.0 (lbs/each)
Product Category	Ac Drives

### Features

display	LCD graphical
Input Voltage	230 V, 208-240 V(-15%, +10%)
keypad	Included

### Dimensions and Weight

Depth	28
Height	17
Width	15

### Descriptions

Description	DG1 230V FR4 N1 20HP 61A CT 25HP 75A VT
extra long description	ETN DG1-32061FN-C21C DG1,230V FR4,N
Features	Demand more flexibility. Eaton's PowerXL DG1 general purpose, variable frequency drives are engineered for today's demanding commercial and industrial applications. With an industry leading energy efficiency algorithm, high short-circuit current rating and robust design, the DG1 offers customers increased efficiency, safety and reliability.
Long Description	Eaton PowerXL DG1 variable frequency drive, 208-240V input 15 kW 20 Hp CT 3PH 50/60 Hz 61A output IP21/type 1 enclosure FR4 LCD Internal EMC filter and DC choke EtherNet, RS-485, BACnet MS/TP, Modbus TCP and RTU ports 2 exp slots
Product Type	DG1, 230V FR4, N1, 20HP, 61A CT, 25HP, 75A VT
Special Features	Coated board

### Manufacturer Information

Brand	Eaton
GTIN	00786685886107
Manufacturers Part Number	DG1-32061FN-C21C
UPC	786685886107



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	DRIVES
Type	Variable Frequency Drive

## Packaging

Carton	1
Weight Per each	80

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Enclosure standard	IP21/type 1 enclosure EN 62061,EN ISO 13849-1,UL Listed,IEC 61508,UL 508C,cUL Listed,CE Marked,GoST-R,RoHS Compliant,C-Tick Compliant