



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DG1347D6FBC21C DG1 480V FR1 N1 5HP 7.6A CT W/ BC Eaton Corp

Catalog Number	DG1347D6FBC21C
Manufacturer	Eaton Corp
Description	Eaton Powerxl DG1 Variable Frequency Drive, 208-240V Input 3 KW 5 HP CT 3PH 50/60 HZ 7.6A Output IP21/Type 1 FR2 LCD Internal Emc Filter and DC Choke Ethernet, RS-485, Bacnet MS/TP, Modbus TCP and Rtu Ports 2 Exp Slots Brake Chopper
Weight per unit	16.0 (lbs/each)
Product Category	Ac Drives

Features

display	LCD graphical
Input Voltage	230 V, 208-240 V(-15%, +10%)
keypad	Included

Dimensions and Weight

Depth	17.5
Height	13
Width	9.5

Descriptions

Description	DG1 480V FR1 N1 5HP 7.6A CT W/ BC
extra long description	ETN DG1-347D6FB-C21C DG1, 480V FR1
Features	Demand more flexibility. Eaton's PowerXL DG1 general purpose, variable frequency drives are engineered for today's demanding commercial and industrial applications. With an industry leading energy efficiency algorithm, high short-circuit current rating and robust design, the DG1 offers customers increased efficiency, safety and reliability.
Long Description	Eaton PowerXL DG1 variable frequency drive, 208-240V input 3 kW 5 Hp CT 3PH 50/60 Hz 7.6A output IP21/type 1 FR2 LCD Internal EMC filter and DC choke EtherNet, RS-485, BACnet MS/TP, Modbus TCP and RTU ports 2 exp slots Brake chopper
Product Type	DG1, 480V FR1 , N1, 5HP (7.6A) CT W/ BC

Manufacturer Information

Brand	Eaton
GTIN	00786685878751
Manufacturers Part Number	DG1-347D6FB-C21C
UPC	786685878751

Taxonomies, Classifications, and Categories

Category Description	DRIVES
Type	Variable Frequency Drive



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	16

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Enclosure standard	IP21/type 1 enclosure UL 508C,cUL Listed,EN 61800-5-1,UL Listed,EN 61800-3,EN ISO 13849-1,IEC 61508,EN 62061,CE Marked,RoHS Compliant,C-Tick Compliant,GoST-R