



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## General Duty Cartridge Fuse Safety Switch

**DG325NRK**

**UPC:**782113639215

### Dimensions:

- **Height:** 44.31 IN
- **Length:** 11.16 IN
- **Width:** 22.66 IN

**Weight:**140 LB

**Notes:**Maximum hp ratings apply only when dual element fuses are used

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** General Duty/Cartridge Fuse
- **Amperage Rating:** 400A
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Painted galvanized steel
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible with neutral
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Four-wire
- **Product Category:** General Duty Safety Switch
- **Voltage Rating:** 240V

### Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - DG325NRK](#)

### Certifications:

- UL Listed

**Product compliance:** No Data







Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## General Duty Cartridge Fuse Safety Switch

DG325NRK

UPC:782113639215

### Dimensions:

- **Height:** 44.31 IN
- **Length:** 11.16 IN
- **Width:** 22.66 IN

**Weight:**140 LB

**Notes:**Maximum hp ratings apply only when dual element fuses are used

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** General Duty/Cartridge Fuse
- **Amperage Rating:** 400A
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Painted galvanized steel
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible with neutral
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Four-wire
- **Product Category:** General Duty Safety Switch
- **Voltage Rating:** 240V

### Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - DG325NRK](#)

### Certifications:

- UL Listed

**Product compliance:** No Data



