



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DH222NGK 60A/2P HD Fusible Safety Switch W/Neut 240V Nema 1

Eaton Corp

Catalog Number	DH222NGK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Fused Safety Switch, 60 A, Nema 1, Painted Steel, Class H, Fusible With Neutral, Two-Pole, Three-Wire, 240 V, Max HP: 3, 7.5 HP/10, 15 HP/10 HP (1, 3PH @ STD Fuse/Time Delay/250 VDC), #14-#2 Cu/Al
Weight per unit	17.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

Features

amperage rating	60
Material	Painted Steel
media	Yes
Poles	2
Voltage Rating	240V

Dimensions and Weight

Depth	16.5
Height	8.31
Width	9.12

Descriptions

Description	60A/2P HD FUSIBLE SAFETY SWITCH W/NEUT 240V NEMA 1
extra long description	ETN DH222NGK 60A/2P HD FUSIBLE Sfty
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw fused safety switch, 60 A, NEMA 1, Painted steel, Class H, Fusible with neutral, Two-pole, Three-wire, 240 V, Max Hp: 3, 7.5 hp/10, 15 hp/10 hp (1,3PH @ Std fuse/time delay/250 Vdc), #14-#2 Cu/Al
Product Type	60A/2P HD Fusible Sfty SW W/Neut 240V N1

Manufacturer Information

Brand	Eaton
GTIN	00782113205779
Manufacturers Part Number	DH222NGK
UPC	782113205779



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description DISCONNECTS

Type Fusible safety switch

Packaging

Carton 1

Weight Per each 17

Uses, Certifications, and Standards

Application Commercial / Institutional Buildings / Structures - Power
Distribution and Controls

nema rating 1

standard CSA Certified,UL Listed,NEC 230.62 (C) Compliant Barrier