



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DH261URK 30A/2P HD NF Safety Switch 600V Nema 3R

Eaton Corp

Catalog Number	DH261URK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Non-Fused Safety Switch, Single-Throw, 30 A, Nema 3R, Painted Galvanized Steel, Non-Fusible, Two-Pole, Two-Wire, 3 At 240 Vac TD 1 PH, 7.5 At 480 Vac TD 1 PH, 10 At 600 Vac TD 1 PH, 15 At 600 VDC
Weight per unit	16.0 (lbs/each)
Product Category	Non-Fusible Heavy Duty Safety

Features

amperage rating	30
dimensions	9.8900 IN X 8.8700 IN X 15.8100 IN
Material	Galvanized Steel
media	Yes
Poles	2
Voltage Rating	600 V

Dimensions and Weight

Depth	9.89
Height	15.81
Width	8.87

Descriptions

Description	30A/2P HD NF SAFETY SWITCH 600V NEMA 3R
extra long description	ETN DH261URK 30A/2P HD NF Sfty Sw 6
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw non-fused safety switch, Single-throw, 30 A, NEMA 3R, Painted galvanized steel, Non-Fusible, Two-pole, Two-wire, 3 at 240 Vac TD 1 Ph, 7.5 at 480 Vac TD 1 Ph, 10 at 600 Vac TD 1 Ph, 15 at 600 Vdc
Product Type	30A/2P HD NF Sfty SW 600V N3R

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685176635
Manufacturers Part Number	DH261URK
UPC	786685176635



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Non-Fusible Safety Switch

Packaging

Carton	1
Weight Per each	16

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and Controls
nema rating	3R
standard	UL Listed,NEC 230.62 (C) Compliant Barrier