



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DH322FRK 60A/3P HD Fusible Safety Switch 240V Nema 3R

Eaton Corp

Catalog Number	DH322FRK
Manufacturer	Eaton Corp
Description	Eaton Enhanced Visible Blade Single-Throw Safety Switch, 60 A, Nema 3R, Painted Galvanized Steel, Class H, Three-Pole, Three-Wire, 240 V, Max HP: 3, 7.5/ 10, 15/ 10 HP (1, 3PH @STD/TD/250 VDC), #14-#2 Cu/Al
Weight per unit	19.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

### Features

amperage rating	60A
dimensions	16.5000 IN X 9.5000 IN X 16.2700 IN
Material	Painted galvanized steel
media	Yes
Poles	Three-pole
Voltage Rating	240V

### Dimensions and Weight

Depth	16.5000
Height	16.2700
Width	9.5000

### Descriptions

Description	60A/3P HD FUSIBLE SAFETY SWITCH 240V NEMA 3R
extra long description	ETN DH322FRK 60A/3P HD FUSIBLE Sfty
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Enhanced visible blade single-throw safety switch, 60 A, NEMA 3R, Painted galvanized steel, Class H, Three-pole, Three-wire, 240 V, Max Hp: 3, 7.5/ 10, 15/ 10 hp (1,3PH @Std/TD/250 Vdc), #14-#2 Cu/Al
Product Type	60A/3P HD Fusible Sfty SW 240V N3R

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113205816
Manufacturers Part Number	DH322FRK
UPC	782113205816



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... DISCONNECTS

Type ..... Fusible safety switch

## Packaging

Carton ..... 1

Weight Per each ..... 19

## Uses, Certifications, and Standards

Application ..... Commercial / Institutional Buildings / Structures - Power  
Distribution and Controls

nema rating ..... Nema 3R

standard ..... UL Listed