



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DH361NGK 30A/3P HD Fusible Safety Switch 600V W/Neut Nema 1

Eaton Corp

Catalog Number	DH361NGK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Fused Safety Switch, 30 A, Nema 1, Painted Steel, Class H, Fusible With Neutral, Three-Pole, Four-Wire, 600 V, Max HP: 7.5, 10/ 15, 20 HP (1/3PH @480, 600 V), #14-#2 Cu/Al
Weight per unit	17.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

### Features

amperage rating	30
Material	Painted Steel
media	Yes
Poles	3
Voltage Rating	600 V

### Dimensions and Weight

Depth	16.5
Height	8.5
Width	9.5

### Descriptions

Description	30A/3P HD FUSIBLE SAFETY SWITCH 600V W/NEUT NEMA 1
extra long description	ETN DH361NGK 30A/3P HD FUSIBLE Sfty
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw fused safety switch, 30 A, NEMA 1, Painted steel, Class H, Fusible with neutral, Three-pole, Four-wire, 600 V, Max Hp: 7.5, 10/ 15, 20 hp (1/3PH @480, 600 V), #14-#2 Cu/Al
Product Type	30A/3P HD Fusible Sfty SW 600V W/Neut N1

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113205526
Manufacturers Part Number	DH361NGK
UPC	782113205526

### Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Fusible safety switch



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	17

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and Controls
nema rating	1
standard	UL Listed, NEC 230.62 (C) Compliant Barrier