



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DH364UGK 200A/3P HD NF Safety Switch 600V Nema 1

*Eaton Corp*

Catalog Number	DH364UGK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Non-Fused Safety Switch, Single-Throw, 200A, Nema 1, Painted Steel, Non-Fusible, Three-Pole, Three-Wire, 15 At 240 Vac TD 1 PH, 50 At 480 Vac TD 1 PH, 50 At 600 Vac TD 1 PH, 60 At 240 Vac TD 3 PH
Weight per unit	43.0 (lbs/each)
Product Category	Non-Fusible Heavy Duty Safety

### Features

amperage rating	200
Material	Painted Steel
media	Yes
Poles	3
Voltage Rating	600 V

### Dimensions and Weight

Depth	11.26
Height	27.66
Width	16

### Descriptions

Description	200A/3P HD NF SAFETY SWITCH 600V NEMA 1
extra long description	ETN DH364UGK 200A/3P HD NF Sfty Sw
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw non-fused safety switch, Single-throw, 200A, NEMA 1, Painted steel, Non-Fusible, Three-pole, Three-wire, 15 at 240 Vac TD 1 Ph, 50 at 480 Vac TD 1 Ph, 50 at 600 Vac TD 1 Ph, 60 at 240 Vac TD 3 Ph
Product Type	200A/3P HD NF Sfty SW 600V N1

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113206806
Manufacturers Part Number	DH364UGK
UPC	782113206806

### Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Non-Fusible Safety Switch



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	43

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and Controls
nema rating	1
standard	UL 98, NEC 230.62 (C) Compliant Barrier