



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DH365FGK 400A/3P HD Fusible Safety Switch 600V Nema 1

Eaton Corp

Catalog Number	DH365FGK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Fused Safety Switch, 400 A, Nema 1, Painted Steel, Class H, Fusible Without Neutral, Three-Pole, Three-Wire, 600 V, Max HP: 250, 350 HP (3PH @480/600 V), (2)#1/0-(2)300 Kcmil; or (1)#1/0-(1)750 Kcmil Al
Weight per unit	105.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

Features

amperage rating	400
dimensions	45.5000 IN X 24.3800 IN X 10.2500 IN
Material	Painted Steel
media	Yes
Poles	3
Voltage Rating	600 V

Dimensions and Weight

Depth	45.5000
Height	10.2500
Width	24.3800

Descriptions

Description	400A/3P HD FUSIBLE SAFETY SWITCH 600V NEMA 1
extra long description	ETN DH365FGK 400A/3P HD Fusible Sft
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw fused safety switch, 400 A, NEMA 1, Painted steel, Class H, Fusible without neutral, Three-pole, Three-wire, 600 V, Max Hp: 250, 350 hp (3PH @480/600 V), (2)#1/0-(2)300 kcmil; or (1)#1/0-(1)750 kcmil Al
Product Type	400A/3P HD Fusible Sfty SW 600V N1

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113207209
Manufacturers Part Number	DH365FGK
UPC	782113207209



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description DISCONNECTS

Type Fusible safety switch

Packaging

Carton 1

Weight Per each 105

Uses, Certifications, and Standards

Application Commercial / Institutional Buildings / Structures - Power
Distribution and Controls

nema rating 1

standard UL Listed, NEC 230.62 (C) Compliant Barrier