



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DH366NRK 600A/3P HD Fusible Safety Switch 600V W/Neut Nema

Eaton Corp

Catalog Number	DH366NRK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Fused Safety Switch, 600 A, Nema 3R, Painted Galvanized Steel, Class H, Neutral, Three-Pole, Four-Wire, 600 V, Max HP: 200, 400, 500 HP (3PH @240, 480, 600 V), (1)#2-(1)600 Kcmil; and (1)#1/0-(1)750 Kcmil Al
Weight per unit	153.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

### Features

amperage rating	600
Material	Galvanized Steel
media	Yes
Poles	3
Voltage Rating	600 V

### Dimensions and Weight

Depth	58
Height	12
Width	27.5

### Descriptions

Description	600A/3P HD FUSIBLE SAFETY SWITCH 600V W/NEUT NEMA
extra long description	ETN DH366NRK 600A/3P HD FSBL Sfty S
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw fused safety switch, 600 A, NEMA 3R, Painted galvanized steel, Class H, Neutral, Three-pole, Four-wire, 600 V, Max Hp: 200, 400, 500 hp (3PH @240,480,600 V), (1)#2-(1)600 kcmil; and (1)#1/0-(1)750 kcmil Al
Product Type	600A/3P HD FSBL Sfty SW 600V W/Neut N3R

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113207605
Manufacturers Part Number	DH366NRK
UPC	782113207605

### Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Fusible safety switch



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	153

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and Controls
nema rating	3R
standard	UL Listed, NEC 230.62 (C) Compliant Barrier